

## SnapStak® Hanger for 7/8 in coaxial cable



### Product Classification

<b>Brand</b>	SnapStak®
<b>Product Type</b>	Hanger kit

### Dimensions

<b>Nominal Size</b>	7/8 in
<b>Compatible Diameter, maximum</b>	30.988 mm   1.220 in
<b>Compatible Diameter, minimum</b>	26.670 mm   1.050 in
<b>Height</b>	41.00 mm   1.61 in
<b>Length</b>	64.00 mm   2.52 in
<b>Width</b>	40.00 mm   1.57 in

### Electrical Specifications

<b>DTF Effect</b>	0.1 dB
<b>Return Loss Effect</b>	0.1 dB

### Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

### General Specifications

<b>Hanger Type</b>	Snap-in hanger
<b>Cables per Hanger</b>	1
<b>Color</b>	Silver
<b>Material Type</b>	Stainless steel
<b>Maximum Stack Height</b>	3
<b>Ordering Note</b>	CommScope® standard product in Asia Pacific   CommScope® standard product in Mexico, Central America, and South America   CommScope® standard product in the United States and Canada
<b>Package Quantity</b>	10

# SSH-78

---

## Mechanical Specifications

<b>Corrosion Resistance, minimum with no degradation</b>	≥500 hours in salt spray chamber
<b>Mounting</b>	3/4 in drilled cable ladder
<b>Vibration Survival</b>	≥4 hours at resonant frequency
<b>Environmental Strength Capability</b>	Double cable weight

## Packed Dimensions

<b>Height</b>	15.6 cm   6.1 in
<b>Length</b>	10.8 cm   4.3 in
<b>Shipping Weight</b>	0.42 kg   0.93 lb
<b>Width</b>	14.8 cm   5.8 in

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power