

26985A



Lace-up Hoisting Grip for 3 in coaxial cable and elliptical waveguide 28 and 34

Product Classification

Product Type Hoisting grip

Dimensions

Nominal Size 3 in
Grip Length, minimum 762.00 mm | 30.00 in
Leader Length, minimum 457.20 mm | 18.00 in
Waveguide Size WR229 | WG11 | R40

Electrical Specifications

DTF Effect 0.1 dB
Return Loss Effect 0.1 dB

General Specifications

Hoisting Grip Type Lace-up hoisting grip
Attachment Spacing Intervals 61 m | 200 ft
Cable Type Corrugated | Elliptical waveguide
Material Type Tin-coated bronze
Ordering Note CommScope® non-standard product
Package Quantity 1
Support Clamp Not included
Tool Type Hoisting grip

Mechanical Specifications

Pull Load Capacity 500 lb

Packed Dimensions

Shipping Weight 1.43 kg | 3.15 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

