



Single Hanger Kit for 1-5/8 in coaxial cable, triple stack; includes hardware and angle adapter

Product Classification

| | |
|---------------------|------------|
| Brand | ValuSite™ |
| Product Type | Hanger kit |

Dimensions

| | |
|-------------------------------------|----------------------|
| Nominal Size | 1-5/8 in |
| Compatible Diameter, maximum | 50.800 mm 2.000 in |
| Compatible Diameter, minimum | 49.022 mm 1.930 in |
| Height | 236.76 mm 9.32 in |
| Length | 90.46 mm 3.56 in |
| Width | 25.92 mm 1.02 in |

Electrical Specifications

| | |
|---------------------------|--------|
| DTF Effect | 0.1 dB |
| Return Loss Effect | 0.1 dB |

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Operating Temperature | -40 °C to +85 °C (-40 °F to +185 °F) |
|------------------------------|--------------------------------------|

General Specifications

| | |
|-----------------------------|--------------------------------------|
| Hanger Type | Composite clamp |
| Cables per Hanger | 3 |
| Color | Black |
| Includes | Angle adapter Hardware |
| Material Type | Engineered plastic Stainless steel |
| Maximum Stack Height | 3 |
| Ordering Note | CommScope® non-standard product |
| Package Quantity | 1 |

Mechanical Specifications

| | |
|--|--|
| Corrosion Resistance, minimum with no degradation | ≥500 hours in salt spray chamber |
| Mounting | M8 hardware |
| UV Resistance, minimum with no degradation | ≥100 hours exposure in accelerated UV life chamber |
| Vibration Survival | ≥4 hours at resonant frequency |
| Environmental Strength Capability | Double cable weight |

Packed Dimensions

| | |
|------------------------|-------------------|
| Height | 38.1 cm 15.0 in |
| Length | 7.6 cm 3.0 in |
| Shipping Weight | 0.57 kg 1.25 lb |
| Width | 38.1 cm 15.0 in |

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power