



Lace-up Hoisting Grip for 1-5/8 in coaxial cable and elliptical waveguide 44, 52, and 63

Product Classification

Product Type Hoisting grip

Dimensions

Nominal Size 1-5/8 in
Grip Length, minimum 685.80 mm | 27.00 in
Leader Length, minimum 304.80 mm | 12.00 in

Electrical Specifications

DTF Effect 0.1 dB
Return Loss Effect 0.1 dB

General Specifications

Hoisting Grip Type Lace-up hoisting grip
Attachment Spacing Intervals 61 m | 200 ft
Material Type Stainless steel
Ordering Note CommScope® standard product in the United States and Canada
Package Quantity 1
Support Clamp Not included
Tool Type Hoisting grip

Mechanical Specifications

Pull Load Capacity 950 lb

Packed Dimensions

Height 3.8 cm | 1.5 in
Length 24.0 cm | 9.4 in
Width 22.4 cm | 8.8 in
Shipping Weight 0.40 kg | 0.88 lb

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
China RoHS SJ/T 11364-2014	Below Maximum Concentration Value (MCV)

