

Fiber indoor/outdoor cable, LightScope® ZWP, Single Jacket All-Dielectric, Riser Rated, 96 fiber, Gel-Free, Stranded Loose Tube, Singlemode + Multimode OM3, Feet jacket marking, Black jacket color


#### Product Classification

| Regional Availability        | Asia   Australia/New Zealand   Latin America   Middle East<br>/Africa   North America |
|------------------------------|---|
| Portfolio                    | CommScope®  |
| Product Type                 | Fiber indoor/outdoor cable  |
| Product Series               | R-LN  |
| General Specifications       |   |
| Cable Type                   | Stranded loose tube   |
| Construction Type            | Non-armored   |
| Subunit Type                 | Gel-free  |
| Jacket Color                 | Black   |
| Jacket Marking               | Feet  |
| Subunit, quantity            | 8   |
| Fibers per Subunit, quantity | 12  |
| Composite Fiber Count        | 48 + 48   |
| Total Fiber Count            | 96  |
| Dimensions                   |   |
| Buffer Tube/Subunit Diameter | 2.5 mm   0.098 in   |
| Diameter Over Jacket         | 13.5 mm   0.531 in  |
|                              |   |

#### Representative Image

Page 1 of 9





### Mechanical Specifications

| Minimum Bend Radius, loaded       | 202 mm   7.953 in  |
|-----------------------------------|--|
| Minimum Bend Radius, unloaded     | 134 mm   5.276 in  |
| Tensile Load, long term, maximum  | 800 N   179.847 lbf  |
| Tensile Load, short term, maximum | 2700 N   606.984 lbf   |
| Compression                       | 22 N/mm   125.623 lb/in  |
| Compression Test Method           | FOTP-41   IEC 60794-1 E3   |
| Flex                              | 25 cycles  |
| Flex Test Method                  | FOTP-104   IEC 60794-1 E6  |
| Impact                            | 4.41 N-m   39.032 in lb  |
| Impact Test Method                | FOTP-25   IEC 60794-1 E4   |
| Strain                            | See long and short term tensile loads  |
| Strain Test Method                | FOTP-33   IEC 60794-1 E1   |
| Twist                             | 10 cycles  |
| Twist Test Method                 | FOTP-85   IEC 60794-1 E7   |
| Vertical Rise, maximum            | 500 m   1,640.42 ft  |
| Optical Specifications            |  |
| Fiber Type                        | Composite MM/SM   G.652.D and G.657.A1   G.652.D and G.657.A1,<br>TeraSPEED®   OM3, LazrSPEED® 300   OS2 |

#### **Environmental Specifications**

Installation temperature

**Operating Temperature** 

-10 °C to +60 °C (+14 °F to +140 °F) -40 °C to +70 °C (-40 °F to +158 °F)

Page 2 of 9



| Storage Temperature           | -40 °C to +75 °C (-40 °F to +167 °F)               |
|-------------------------------|--|
| Cable Qualification Standards | ANSI/ICEA S-104-696   EN 187105   Telcordia GR-409 |
| Environmental Space           | Riser  |
| Flame Test Listing            | NEC OFNR (ETL) and c(ETL)                          |
| Flame Test Method             | UL 1666  |
| Jacket UV Resistance          | UV stabilized                                      |
| Water Penetration             | 24 h   |
| Water Penetration Test Method | FOTP-82   IEC 60794-1 F5                           |

#### **Environmental Test Specifications**

| Cable Freeze                  | -2 °C   28.4 °F                      |
|-------------------------------|--------------------------------------|
| Cable Freeze Test Method      | FOTP-98   IEC 60794-1 F15            |
| Heat Age                      | -40 °C to +85 °C (-40 °F to +185 °F) |
| Heat Age Test Method          | IEC 60794-1 F9                       |
| Low High Bend                 | -30 °C to +60 °C (-22 °F to +140 °F) |
| Low High Bend Test Method     | FOTP-37   IEC 60794-1 E11            |
| Temperature Cycle             | -40 °C to +70 °C (-40 °F to +158 °F) |
| Temperature Cycle Test Method | FOTP-3   IEC 60794-1 F1              |
|                               |                                      |

#### Packaging and Weights

**Cable weight** 

164 kg/km | 110.203 lb/kft

#### Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC    | Compliant as per SVHC revision on www.commscope.com/ProductCompliance          |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |
|               |  |



#### Included Products

CS-5L-LT

 LazrSPEED® 300 OM3 Bend-Insensitive Multimode Fiber

Page 3 of 9



CS-8W-IOLT – TeraSPEED® OS2 Singlemode Fiber

#### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

Page 4 of 9



### LazrSPEED® 300

LazrSPEED® 300 OM3 Bend-Insensitive Multimode Fiber

#### Product Classification

**Numerical Aperture** 

| Portfolio                                     | CommScope®             |
|---|------------------------|
| Product Type                                  | Optical fiber          |
| General Specifications                        |                        |
| Cladding Diameter                             | 125 µm                 |
| Cladding Diameter Tolerance                   | ±5 μm                  |
| Cladding Non-Circularity, maximum             | 1 %                    |
| Coating Diameter (Colored)                    | 254 µm                 |
| Coating Diameter (Uncolored)                  | 245 µm                 |
| Coating Diameter Tolerance (Colored)          | ±7 μm                  |
| Coating Diameter Tolerance (Uncolored)        | ±10 µm                 |
| Coating/Cladding Concentricity Error, maximum | 12 µm                  |
| Core Diameter                                 | 50 µm                  |
| Core Diameter Tolerance                       | ±2.5 μm                |
| Core/Clad Offset, maximum                     | 1.5 μm                 |
| Proof Tensile Stress                          | 100,000 psi (0.69 GPa) |
| Mechanical Specifications                     |                        |

| Macrobending, 15 mm Ø mandrel, 2 turns   | 0.20 dB @ 850 nm   0.50 dB @ 1,300 nm |
|--|---------------------------------------|
| Macrobending, 30 mm Ø mandrel, 2 turns   | 0.10 dB @ 850 nm   0.30 dB @ 1,300 nm |
| Macrobending, 75 mm Ø mandrel, 100 turns | 0.50 dB @ 1,300 nm   0.50 dB @ 850 nm |
| Coating Strip Force, maximum             | 8.9 N   2.001 lbf                     |
| Coating Strip Force, minimum             | 1.3 N   0.292 lbf                     |
| Dynamic Fatigue Parameter, minimum       | 18                                    |
| Optical Specifications                   |                                       |

Page 5 of 9

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 30, 2025

0.2



### CS-5L-LT

| Numerical Aperture Tolerance        | ±0.015              |
|-------------------------------------|---------------------|
| Point Defects, maximum              | 0.15 dB             |
| Zero Dispersion Slope, maximum      | 0.105 ps/[km-nm-nm] |
| Zero Dispersion Wavelength, maximum | 1316 nm             |
| Zero Dispersion Wavelength, minimum | 1297 nm             |

#### Optical Specifications, Wavelength Specific

| 1 Gbps Ethernet Distance     | 1,020 m @ 850 nm   600 m @ 1,300 nm                           |
|------------------------------|---|
| 10 Gbps Ethernet Distance    | 300 m @ 850 nm  |
| Attenuation, maximum         | 1.00 dB/km @ 1,300 nm   3.00 dB/km @ 850 nm                   |
| Backscatter Coefficient      | -68.0 dB @ 850 nm   -75.7 dB @ 1,300 nm                       |
| Bandwidth, Laser, minimum    | 2,000 MHz-km @ 850 nm   500 MHz-km @ 1,300 nm                 |
| Bandwidth, OFL, minimum      | 1,500 MHz-km @ 850 nm   500 MHz-km @ 1,300 nm                 |
| Differential Mode Delay      | 0.70 ps/m @ 850 nm  |
| Differential Mode Delay Note | Superior to ANSI/TIA TIA-492AAAF and IEC 60793-2-10 at 850 nm |
| Index of Refraction          | 1.479 @ 1,300 nm   1.483 @ 850 nm                             |
| Standards Compliance         | ANSI/TIA-492AAAF (OM3)  |

#### **Environmental Specifications**

| Heat Aging, maximum                   | 0.20 dB/km @ 85 °C |
|---------------------------------------|--------------------|
| Temperature Dependence, maximum       | 0.1 dB/km          |
| Temperature Humidity Cycling, maximum | 0.2 dB/km          |
| Water Immersion, maximum              | 0.20 dB/km @ 23 °C |

#### Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

#### \* Footnotes

| Temperature Dependence, maximum       | Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)       |
|---------------------------------------|---|
| Temperature Humidity Cycling, maximum | Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F) |
|                                       | up to 95% relative humidity   |

Page 6 of 9



# TeraSPEED®

#### TeraSPEED® OS2 Singlemode Fiber

#### Product Classification

| Portfolio                                     | CommScope®                              |  |
|---|---|--|
| Product Type                                  | Optical fiber                           |  |
| General Specifications                        |   |  |
| Cladding Diameter                             | 125 µm                                  |  |
| Cladding Diameter Tolerance                   | ±0.7 μm                                 |  |
| Cladding Non-Circularity, maximum             | 0.7 %                                   |  |
| Coating Diameter (Colored)                    | 249 µm                                  |  |
| Coating Diameter (Uncolored)                  | 242 µm                                  |  |
| Coating Diameter Tolerance (Colored)          | ±13 μm                                  |  |
| Coating Diameter Tolerance (Uncolored)        | ±5 μm                                   |  |
| Coating/Cladding Concentricity Error, maximum | 12 µm                                   |  |
| Core Diameter                                 | 8.3 µm                                  |  |
| Core/Clad Offset, maximum                     | 0.5 µm                                  |  |
| Proof Tensile Stress                          | 100,000 psi (0.69 GPa)                  |  |
| Dimensions                                    |   |  |
| Fiber Curl, minimum                           | 4 m   13.123 ft                         |  |
| Mechanical Specifications                     |   |  |
| Macrobending, 20 mm Ø mandrel, 1 turn         | 0.75 dB @ 1,550 nm   1.50 dB @ 1,625 nm |  |
| Macrobending, 30 mm Ø mandrel, 10 turns       | 0.25 dB @ 1,550 nm   1.00 dB @ 1,625 nm |  |
| Macrobending, 60 mm Ø mandrel, 100 turns      | 0.05 dB @ 1,550 nm   0.05 dB @ 1,625 nm |  |
| Coating Strip Force, maximum                  | 8.9 N   2.001 lbf                       |  |
| Coating Strip Force, minimum                  | 1.3 N   0.292 lbf                       |  |
| Dynamic Fatigue Parameter, minimum            | 20                                      |  |

Page 7 of 9



### CS-8W-IOLT

#### **Optical Specifications**

| Cabled Cutoff Wavelength, maximum                       | 1260 nm   |
|---|---|
| Point Defects, maximum                                  | 0.1 dB  |
| Zero Dispersion Slope, maximum                          | 0.092 ps/[km-nm-nm]   |
| Zero Dispersion Wavelength, maximum                     | 1324 nm   |
| Zero Dispersion Wavelength, minimum                     | 1300 nm   |
| Optical Specifications, Wavelength Specific             |   |
| Attenuation, maximum                                    | 0.22 dB/km @ 1,550 nm   0.25 dB/km @ 1,490<br>nm   0.25 dB/km @ 1,625 nm   0.36 dB/km @ 1,310<br>nm   0.36 dB/km @ 1,385 nm |
| Attenuation, typical                                    | 0.19 dB/km @ 1,550 nm   0.33 dB/km @ 1,310 nm   |
| Backscatter Coefficient                                 | -79.6 dB @ 1,310 nm   -82.1 dB @ 1,550 nm   |
| Dispersion, maximum                                     | 18 ps(nm-km) at 1550 nm   3.5 ps(nm-km) from 1285<br>nm to 1330 nm at 1310 nm   |
| Index of Refraction                                     | 1.467 @ 1,310 nm   1.467 @ 1,385 nm   1.468 @ 1,550<br>nm   |
| Mode Field Diameter                                     | 10.4 μm @ 1,550 nm   9.2 μm @ 1,310 nm   9.6 μm @<br>1,385 nm   |
| Mode Field Diameter Tolerance                           | ±0.4 μm @ 1310 nm   ±0.5 μm @ 1550 nm   ±0.6 μm<br>@ 1385 nm  |
| Polarization Mode Dispersion Link Design Value, maximum | 0.04 ps/sqrt(km)  |
| Standards Compliance                                    | ITU-T G.652.D   ITU-T G.657.A1   TIA-492CAAB (OS2)  |

#### Environmental Specifications

| Heat Aging, maximum                   | 0.05 dB/km @ 85 °C |
|---------------------------------------|--------------------|
| Temperature Dependence, maximum       | 0.05 dB/km         |
| Temperature Humidity Cycling, maximum | 0.05 dB/km         |
| Water Immersion, maximum              | 0.05 dB/km @ 23 °C |

#### Regulatory Compliance/Certifications

Classification

#### Agency

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

#### \* Footnotes

Page 8 of 9



### CS-8W-IOLT

Temperature Dependence, maximum Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

Temperature Humidity Cycling, maximum Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

up to 95% relative humidity

Page 9 of 9

