



Fiber indoor/outdoor cable, 12-fiber, Multimode OM4, Gel-free, Meters jacket marking, Black jacket color, Dca flame rating, 2000 m. Provides Rodent Resistance

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber indoor/outdoor cable
<b>Product Series</b>	C-CN

## General Specifications

<b>Cable Type</b>	Loose tube
<b>Subunit Type</b>	Gel-free
<b>Jacket Color</b>	Black
<b>Jacket Marking</b>	Meters
<b>Jacket Marking Method</b>	Inkjet
<b>Jacket Marking Text</b>	COMMSCOPE GB F.O. CABLE 760244295 INT/EXT RODENT RESIST DLT 12X9/125 OS2 EN50575 CLASS D (Serial NUMBER) (METRE MARK)
<b>Fibers per Subunit, quantity</b>	12
<b>Total Fiber Count</b>	12

## Dimensions

<b>Cable Length</b>	2000 m   6,561.68 ft
<b>Diameter Over Jacket</b>	6.4 mm   0.252 in

## Mechanical Specifications

<b>Minimum Bend Radius, loaded</b>	139.7 mm   5.5 in
<b>Minimum Bend Radius, unloaded</b>	129.5 mm   5.098 in
<b>Tensile Load, long term, maximum</b>	650 N   146.126 lbf
<b>Tensile Load, short term, maximum</b>	1250 N   281.011 lbf

## Optical Specifications

# 760244293 | C-012-CN-5K-M12BK/28D/GY/D

---

**Fiber Type** OM4

## Optical Specifications, Wavelength Specific

**Attenuation, maximum** 0.35 dB/km @ 1,300 nm | 0.35 dB/km @ 1,550 nm | 0.45 dB/km @ 1,310 nm

**Standards Compliance** IEC 60794-1 | TIA-492CAAB (OS2)

## Environmental Specifications

**Installation temperature** -5 °C to +50 °C (+23 °F to +122 °F)

**Operating Temperature** -10 °C to +70 °C (+14 °F to +158 °F)

**Storage Temperature** -10 °C to +70 °C (+14 °F to +158 °F)

**EN50575 CPR Cable EuroClass Fire Performance** Dca

**EN50575 CPR Cable EuroClass Smoke Rating** s2

**EN50575 CPR Cable EuroClass Droplets Rating** d2

**EN50575 CPR Cable EuroClass Acidity Rating** a1

**Environmental Space** Universal Low Smoke Zero Halogen (ULSZH)

## Packaging and Weights

**Cable weight** 47 kg/km | 31.583 lb/kft

## Included Products

CS-8W-250-EMEA – LightScope ZWP® Singlemode Fiber  
250um

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

## LightScope ZWP® Singlemode Fiber



### Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Optical fiber

### General Specifications

<b>Cladding Diameter</b>	125 µm
<b>Cladding Diameter Tolerance</b>	±0.7 µm
<b>Cladding Non-Circularity, maximum</b>	0.7 %
<b>Coating Diameter (Colored)</b>	249 µm
<b>Coating Diameter (Uncolored)</b>	242 µm
<b>Coating Diameter Tolerance (Colored)</b>	±13 µm
<b>Coating Diameter Tolerance (Uncolored)</b>	±5 µm
<b>Coating/Cladding Concentricity Error, maximum</b>	12 µm
<b>Core/Clad Offset, maximum</b>	0.5 µm
<b>Proof Test</b>	689.476 N/mm <sup>2</sup>   100000 psi

### Dimensions

<b>Fiber Curl, minimum</b>	4 m   13.123 ft
----------------------------	-----------------

### Mechanical Specifications

<b>Macrobending, 20 mm Ø mandrel, 1 turn</b>	0.75 dB @ 1,550 nm   1.50 dB @ 1,625 nm
<b>Macrobending, 30 mm Ø mandrel, 10 turns</b>	0.25 dB @ 1,550 nm   1.00 dB @ 1,625 nm
<b>Macrobending, 60 mm Ø mandrel, 100 turns</b>	0.05 dB @ 1,550 nm   0.05 dB @ 1,625 nm
<b>Coating Strip Force, maximum</b>	8.9 N   2.001 lbf
<b>Coating Strip Force, minimum</b>	1.3 N   0.292 lbf

# CS-8W-250-EMEA | 250um

**Dynamic Fatigue Parameter, minimum** 20

## Optical Specifications

**Cabled Cutoff Wavelength, maximum** 1250 nm

**Point Defects, maximum** 0.05 dB

**Zero Dispersion Slope, maximum** 0.092 ps/[km-nm-nm]

**Zero Dispersion Wavelength, maximum** 1324 nm

**Zero Dispersion Wavelength, minimum** 1300 nm

## Optical Specifications, Wavelength Specific

**Attenuation, maximum** 0.21 dB/km @ 1,550 nm | 0.24 dB/km @ 1625 nm | 0.25 dB/km @ 1,490 nm | 0.35 dB/km @ 1,310 nm | 0.35 dB/km @ 1,385 nm

**Dispersion, maximum** 18 ps(nm-km) at 1550 nm | 2.2 ps(nm-km) at 1625 nm | 3.5 ps(nm-km) from 1285 nm to 1330 nm at 1310 nm

**Index of Refraction** 1.467 @ 1,310 nm | 1.468 @ 1,550 nm

**Mode Field Diameter** 10.4  $\mu\text{m}$  @ 1,550 nm | 9.2  $\mu\text{m}$  @ 1,310 nm

**Mode Field Diameter Tolerance**  $\pm 0.4 \mu\text{m}$  @ 1310 nm |  $\pm 0.5 \mu\text{m}$  @ 1550 nm

**Polarization Mode Dispersion Link Design Value, maximum** 0.06 ps/sqrt(km)

**Standards Compliance** ITU-T G.652.D | ITU-T G.657.A1

## Environmental Specifications

**Heat Aging, maximum** 0.05 dB/km @ 85 °C

**Temperature Dependence, maximum** 0.05 dB/km

**Temperature Humidity Cycling, maximum** 0.05 dB/km

**Water Immersion, maximum** 0.05 dB/km @ 23 °C

## \* Footnotes

**Temperature Dependence, maximum** Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

**Temperature Humidity Cycling, maximum** Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F) up to 95% relative humidity