

760257072 | PPL-CM-12AU-24AP-4X3-SM-BQU



Propel ULL Singlemode Conversion Module, (4) MPO-12/APC non-pinned ports rear, (3) MPO-24/APC (16 fiber) pinned ports front, QSFP-DD

- Ultra-low loss (ULL) with Method B Enhanced polarity
- Can be installed and removed from front or rear of panel
- Serialized QR code provides easy access to factory optical test results
- This component requires 4 of the 12 lanes on the Propel Panel blade

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | SYSTEMAX® |
| Product Type | Fiber module |
| Product Brand | Propel |
| Product Series | PPL |

General Specifications

| | |
|-------------------------------------|------------------------------------|
| Functionality | Breakout |
| Color, front | Gray |
| Color, rear | Gray |
| Data Module Type | Fiber Conversion Module |
| Interface, front | MPO |
| Interface Feature, front | Internal shutters MPO Pinned |
| Interface, rear | MPO |
| Interface Feature, rear | Internal shutters MPO Non-Pinned |
| Polarity | Method B Enhanced (ULL) |
| Total Fibers, quantity | 48 |
| Total Ports, quantity, front | 3 |
| Total Ports, quantity, rear | 4 |

Dimensions

| | |
|---------------|-------------------|
| Height | 11 mm 0.433 in |
| Width | 131 mm 5.157 in |

760257072 | PPL-CM-12AU-24AP-4X3-SM-BQU

Depth 170 mm | 6.693 in

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A2

Insertion Loss, maximum 0.7 dB

Environmental Specifications

Qualification Standards IEC 61753-1 | TIA-568.3-D

Safety Standard UL 62368

Packaging and Weights

Packaging quantity 1