

# 760257068 | PPL-CM-12U-16AP-4X3-OM5-BEU



Propel ULL Multimode OM5 Conversion Module, (4) MPO-12/UPC non-pinned ports rear, (3) MPO-16/APC pinned ports front

- Ultra-low loss (ULL) with Method B Enhanced polarity
- Can be installed and removed from front or rear of panel
- Serialized QR code provides easy access to factory optical test results
- This component requires 4 of the 12 lanes on the Propel Panel blade

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	SYSTIMAX®
<b>Product Type</b>	Fiber module
<b>Product Brand</b>	Propel
<b>Product Series</b>	PPL

## General Specifications

<b>Functionality</b>	Breakout
<b>Color, front</b>	Gray
<b>Color, rear</b>	Gray
<b>Data Module Type</b>	Fiber Conversion Module
<b>Interface, front</b>	MPO
<b>Interface Feature, front</b>	Internal shutters   MPO Pinned
<b>Interface, rear</b>	MPO
<b>Interface Feature, rear</b>	Internal shutters   MPO Non-Pinned
<b>Polarity</b>	Method B Enhanced (ULL)
<b>Total Fibers, quantity</b>	48
<b>Total Ports, quantity, front</b>	3
<b>Total Ports, quantity, rear</b>	4

## Dimensions

<b>Height</b>	11 mm   0.433 in
<b>Width</b>	131 mm   5.157 in
<b>Depth</b>	170 mm   6.693 in

# 760257068 | PPL-CM-12U-16AP-4X3-OM5-BEU

---

## Optical Specifications

<b>Fiber Mode</b>	Multimode
<b>Fiber Type</b>	G.657.A2   OM5
<b>Insertion Loss, maximum</b>	0.4 dB

## Environmental Specifications

<b>Qualification Standards</b>	IEC 61753-1   TIA-568.3-D
<b>Safety Standard</b>	UL 62368

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---