

Fiber indoor/outdoor cable, LazrSPEED®, Single Jacket All-Dielectric, Plenum Rated, , 12 fiber Multimode OM4, Gel-Free, Stranded Loose Tube, PVDF jacket, Black jacket color, Feet cable marking

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   Latin America   Middle East /Africa   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber indoor/outdoor cable
<b>Product Series</b>	P-LN



## General Specifications

<b>Cable Type</b>	Stranded loose tube
<b>Construction Type</b>	Non-armored
<b>Subunit Type</b>	Gel-free
<b>Filler, quantity</b>	4
<b>Jacket Color</b>	Black
<b>Jacket Marking</b>	Feet
<b>Subunit, quantity</b>	1
<b>Fibers per Subunit, quantity</b>	12
<b>Total Fiber Count</b>	12

## Dimensions

<b>Buffer Tube/Subunit Diameter</b>	2.5 mm   0.098 in
<b>Diameter Over Jacket</b>	9.7 mm   0.382 in

## Representative Image



## Mechanical Specifications

<b>Minimum Bend Radius, loaded</b>	145 mm   5.709 in
<b>Minimum Bend Radius, unloaded</b>	96.5 mm   3.799 in
<b>Tensile Load, long term, maximum</b>	800 N   179.847 lbf
<b>Tensile Load, short term, maximum</b>	2700 N   606.984 lbf
<b>Compression</b>	22 N/mm   125.623 lb/in
<b>Compression Test Method</b>	FOTP-41   IEC 60794-1 E3
<b>Flex</b>	25 cycles
<b>Flex Test Method</b>	FOTP-104   IEC 60794-1 E6
<b>Impact</b>	2.94 N-m   26.021 in lb
<b>Impact Test Method</b>	FOTP-25   IEC 60794-1 E4
<b>Strain</b>	See long and short term tensile loads
<b>Strain Test Method</b>	FOTP-33   IEC 60794-1 E1
<b>Twist</b>	10 cycles

# 760107805 | P-012-LN-5K-F12BK/25D

**Twist Test Method** FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 880 m | 2,887.139 ft

## Optical Specifications

**Fiber Type** OM4, LazrSPEED® 550 | OM4, LazrSPEED® 550

## Environmental Specifications

**Installation temperature** -30 °C to +70 °C (-22 °F to +158 °F)

**Operating Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Storage Temperature** -40 °C to +75 °C (-40 °F to +167 °F)

**Cable Qualification Standards** ANSI/ICEA S-104-696 | EN 187105 | Telcordia GR-409

**Environmental Space** Plenum

**Flame Test Listing** NEC OFNP (ETL) and c(ETL)

**Flame Test Method** NFPA 130 | NFPA 262

**Jacket UV Resistance** UV stabilized

**Water Penetration** 24 h

**Water Penetration Test Method** FOTP-82 | IEC 60794-1 F5

## Environmental Test Specifications

**Cable Freeze** -2 °C | 28.4 °F

**Cable Freeze Test Method** FOTP-98 | IEC 60794-1 F15

**Heat Age** -40 °C to +85 °C (-40 °F to +185 °F)

**Heat Age Test Method** IEC 60794-1 F9

**Low High Bend** -30 °C to +60 °C (-22 °F to +140 °F)

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle** -40 °C to +70 °C (-40 °F to +158 °F)

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

## Packaging and Weights

**Cable weight** 92 kg/km | 61.821 lb/kft

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

## Included Products

CS-5K-LT - LazrSPEED® 550 OM4 Bend-Insensitive Multimode Fiber

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

## LazrSPEED® 550 OM4 Bend-Insensitive Multimode Fiber

### LazrSPEED® 550

#### Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Optical fiber

#### General Specifications

<b>Cladding Diameter</b>	125 µm
<b>Cladding Diameter Tolerance</b>	±0.8 µm
<b>Cladding Non-Circularity, maximum</b>	1 %
<b>Coating Diameter (Colored)</b>	254 µm
<b>Coating Diameter (Uncolored)</b>	245 µm
<b>Coating Diameter Tolerance (Colored)</b>	±7 µm
<b>Coating Diameter Tolerance (Uncolored)</b>	±10 µm
<b>Coating/Cladding Concentricity Error, maximum</b>	12 µm
<b>Core Diameter</b>	50 µm
<b>Core Diameter Tolerance</b>	±2.5 µm
<b>Core/Clad Offset, maximum</b>	1.5 µm
<b>Proof Test</b>	689.476 N/mm <sup>2</sup>   100000 psi

#### Mechanical Specifications

<b>Macrobending, 15 mm Ø mandrel, 2 turns</b>	0.20 dB @ 850 nm   0.50 dB @ 1,300 nm
<b>Macrobending, 30 mm Ø mandrel, 2 turns</b>	0.10 dB @ 850 nm   0.30 dB @ 1,300 nm
<b>Macrobending, 75 mm Ø mandrel, 100 turns</b>	0.50 dB @ 1,300 nm   0.50 dB @ 850 nm
<b>Coating Strip Force, maximum</b>	8.9 N   2.001 lbf
<b>Coating Strip Force, minimum</b>	1.3 N   0.292 lbf
<b>Dynamic Fatigue Parameter, minimum</b>	18

# CS-5K-LT

## Optical Specifications

<b>Numerical Aperture</b>	0.2
<b>Numerical Aperture Tolerance</b>	±0.015
<b>Point Defects, maximum</b>	0.15 dB
<b>Zero Dispersion Slope, maximum</b>	0.105 ps/[km-nm-nm]
<b>Zero Dispersion Wavelength, maximum</b>	1316 nm
<b>Zero Dispersion Wavelength, minimum</b>	1297 nm

## Optical Specifications, Wavelength Specific

<b>1 Gbps Ethernet Distance</b>	1,110 m @ 850 nm   600 m @ 1,300 nm
<b>10 Gbps Ethernet Distance</b>	550 m @ 850 nm
<b>Attenuation, maximum</b>	1.00 dB/km @ 1,300 nm   3.00 dB/km @ 850 nm
<b>Backscatter Coefficient</b>	-68.0 dB @ 850 nm   -75.7 dB @ 1,300 nm
<b>Bandwidth, Laser, minimum</b>	4,700 MHz-km @ 850 nm   500 MHz-km @ 1,300 nm
<b>Bandwidth, OFL, minimum</b>	3,500 MHz-km @ 850 nm   500 MHz-km @ 1,300 nm
<b>Differential Mode Delay</b>	0.70 ps/m @ 850 nm
<b>Differential Mode Delay Note</b>	Superior to ANSI/TIA TIA-492AAAF and IEC 60793-2-10 at 850 nm
<b>Index of Refraction</b>	1.479 @ 1,300 nm   1.483 @ 850 nm
<b>Standards Compliance</b>	ANSI/TIA-492AAAF (OM4)   IEC 60793-2-10, A1 (OM4)

## Environmental Specifications

<b>Heat Aging, maximum</b>	0.20 dB/km @ 85 °C
<b>Temperature Dependence, maximum</b>	0.1 dB/km
<b>Temperature Humidity Cycling, maximum</b>	0.2 dB/km
<b>Water Immersion, maximum</b>	0.20 dB/km @ 23 °C

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

## \* Footnotes

<b>Temperature Dependence, maximum</b>	Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)
<b>Temperature Humidity Cycling, maximum</b>	Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

# CS-5K-LT

---

up to 95% relative humidity