

760259115 | PPL-1U-ANG-FX



Propel 1RU fixed tray angled fiber panel, accepts Propel ULL components, providing up to 72 duplex LC ports, 72 MPO ports or 144 SN ports (288f). For use with 8 fiber, 12 fiber or 24 fiber components

- Components can be installed and removed from front or rear of panel

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber patch panel |
| Product Brand | Propel |
| Product Series | PPL |

General Specifications

| | |
|------------------------------|-----------|
| Color | Gray |
| Interface, front | Unloaded |
| Rack Type | EIA 19 in |
| Rack Units | 1 |
| Shelf Movement | Fixed |
| Total Ports, quantity | 0 |

Dimensions

| | |
|---------------|--------------------|
| Height | 44 mm 1.732 in |
| Width | 483 mm 19.016 in |
| Depth | 236 mm 9.291 in |

Material Specifications

| | |
|----------------------|------------------|
| Material Type | Aluminum Steel |
|----------------------|------------------|

Environmental Specifications

| | |
|------------------------|----|
| Safety Standard | UL |
|------------------------|----|

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

