## 760125229 | N-002-DZ-5L-FSUAQ



Fiber indoor cable, LazrSPEED® Riser/LSZH rated Distribution, interlocking aluminum armored, Multimode OM3, 2 fiber single-unit, Gelfree, Feet jacket marking, Aqua jacket color

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber indoor cable

**Product Series** N-DZ

General Specifications

Armor Type Interlocking aluminum

Cable TypeDistributionConstruction TypeArmored

**Subunit Type** Gel-free

Jacket Color Aqua

Jacket Marking Feet

Total Fiber Count 2


**Dimensions** 

Diameter Over Armor10.8 mm | 0.425 inDiameter Over Jacket12.84 mm | 0.506 in

Representative Image



## 760125229 | N-002-DZ-5L-FSUAQ



#### Mechanical Specifications

Minimum Bend Radius, loaded192 mm7.559 inMinimum Bend Radius, unloaded128 mm5.039 inTensile Load, long term, maximum200 N | 44.962 lbfTensile Load, short term, maximum667 N | 149.948 lbf

 Compression
 85 N/mm | 485.363 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 35 N-m | 309.776 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 161 m | 528.215 ft

**Optical Specifications** 

Fiber Type OM3, LazrSPEED® 300 | OM3, LazrSPEED® 300

#### **Environmental Specifications**

Installation temperature  $-10 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (+14  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

Operating Temperature  $-20 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-4  $^{\circ}\text{F}$  to +158  $^{\circ}\text{F}$ )

Page 2 of 6



## 760125229 | N-002-DZ-5L-FSUAQ

**Storage Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

Cable Qualification StandardsANSI/ICEA S-83-596 | Telcordia GR-409Environmental SpaceLow Smoke Zero Halogen (LSZH) | Riser

Flame Test Listing NEC OFCR-ST1 (ETL) and c(ETL)

Flame Test Method | IEC 60332-3 | IEC 60754-2 | IEC 61034-2 | UL 1666 | UL 1685

#### **Environmental Test Specifications**

**Heat Age**  $-20 \,^{\circ}\text{C}$  to  $+85 \,^{\circ}\text{C}$   $(-4 \,^{\circ}\text{F}$  to  $+185 \,^{\circ}\text{F})$ 

**Heat Age Test Method** IEC 60794-1 F9

**Low High Bend** -10 °C to +60 °C (+14 °F to +140 °F)

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle**  $-20 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-4 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 127 kg/km | 85.34 lb/kft

#### Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

#### Included Products

CS-5L-TB – LazrSPEED® 300 OM3 Bend-Insensitive Multimode

Fiber

#### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable



#### LazrSPEED® 300 OM3 Bend-Insensitive Multimode Fiber

### LazrSPEED® 300

#### **Product Classification**

Portfolio CommScope®
Product Type Optical fiber

#### General Specifications

**Cladding Diameter** 125 µm **Cladding Diameter Tolerance** ±0.8 µm Cladding Non-Circularity, maximum 1 % **Coating Diameter (Colored)**  $254 \, \mu m$ **Coating Diameter (Uncolored)** 245 µm **Coating Diameter Tolerance (Colored)** ±7 µm **Coating Diameter Tolerance (Uncolored)** ±10 μm Coating/Cladding Concentricity Error, maximum 12 µm **Core Diameter** 50 µm **Core Diameter Tolerance** ±2.5 µm

**Proof Test** 689.476 N/mm² | 100000 psi

Tight Buffer Diameter 900  $\mu m$ Tight Buffer Diameter Tolerance  $\pm 40 \ \mu m$ 

### Mechanical Specifications

Core/Clad Offset, maximum

 Macrobending, 15 mm Ø mandrel, 2 turns
 0.20 dB @ 850 nm | 0.50 dB @ 1,300 nm

 Macrobending, 30 mm Ø mandrel, 2 turns
 0.10 dB @ 850 nm | 0.30 dB @ 1,300 nm

 Macrobending, 75 mm Ø mandrel, 100 turns
 0.50 dB @ 1,300 nm | 0.50 dB @ 850 nm

 $1.5 \, \mu m$ 

Coating Strip Force, maximum 8.9 N | 2.001 lbf



## CS-5L-TB

Coating Strip Force, minimum 1.3 N | 0.292 lbf

**Dynamic Fatigue Parameter, minimum** 18

**Optical Specifications** 

Numerical Aperture 0.2

Numerical Aperture Tolerance±0.015Point Defects, maximum0.15 dB

**Zero Dispersion Slope, maximum** 0.105 ps/[km-nm-nm]

**Zero Dispersion Wavelength, maximum** 1316 nm **Zero Dispersion Wavelength, minimum** 1297 nm

Optical Specifications, Wavelength Specific

**1 Gbps Ethernet Distance** 1,020 m @ 850 nm | 600 m @ 1,300 nm

**10 Gbps Ethernet Distance** 300 m @ 850 nm

**Attenuation, maximum** 1.00 dB/km @ 1,300 nm | 3.00 dB/km @ 850 nm

**Backscatter Coefficient** -68.0 dB @ 850 nm | -75.7 dB @ 1,300 nm

 Bandwidth, Laser, minimum
 2,000 MHz-km @ 850 nm | 500 MHz-km @ 1,300 nm

 Bandwidth, OFL, minimum
 1,500 MHz-km @ 850 nm | 500 MHz-km @ 1,300 nm

**Differential Mode Delay** 0.70 ps/m @ 850 nm

Differential Mode Delay Note Superior to ANSI/TIA TIA-492AAAF and IEC 60793-2-10 at 850 nm

**Index of Refraction** 1.479 @ 1,300 nm | 1.483 @ 850 nm

Standards Compliance ANSI/TIA-492AAAF (OM3)

**Environmental Specifications** 

**Heat Aging, maximum** 0.20 dB/km @ 85 °C

Temperature Dependence, maximum0.1 dB/kmTemperature Humidity Cycling, maximum0.2 dB/km

**Water Immersion, maximum** 0.20 dB/km @ 23 °C

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

\* Footnotes

**COMMSCOPE®** 

# CS-5L-TB

**Temperature Dependence, maximum** 

Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

Temperature Humidity Cycling, maximum Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

up to 95% relative humidity

