# 760125237 | N-004-DZ-5L-FSUAQ



Fiber indoor cable, LazrSPEED® Riser/LSZH rated Distribution, interlocking aluminum armored, Multimode OM3, 4 fiber single-unit, Gelfree, Feet jacket marking, Aqua jacket color

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber indoor cable

**Product Series** N-DZ

### General Specifications

Armor Type Interlocking aluminum

Cable TypeDistributionConstruction TypeArmoredSubunit TypeGel-freeJacket ColorAqua

Jacket Marking Feet
Total Fiber Count 4


#### **Dimensions**

Diameter Over Armor10.8 mm | 0.425 inDiameter Over Jacket12.8 mm | 0.504 in

## Representative Image



# 760125237 | N-004-DZ-5L-FSUAQ



### Mechanical Specifications

Minimum Bend Radius, loaded192 mm7.559 inMinimum Bend Radius, unloaded128 mm5.039 inTensile Load, long term, maximum200 N | 44.962 lbfTensile Load, short term, maximum667 N | 149.948 lbf

 Compression
 85 N/mm | 485.363 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 35 N-m | 309.776 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 150 m | 492.126 ft

Optical Specifications

Fiber Type OM3, LazrSPEED® 300 | OM3, LazrSPEED® 300

### **Environmental Specifications**

Installation temperature  $-10 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (+14  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

Operating Temperature  $-20 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-4  $^{\circ}\text{F}$  to +158  $^{\circ}\text{F}$ )

Page 2 of 3



# 760125237 | N-004-DZ-5L-FSUAQ

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Cable Qualification StandardsANSI/ICEA S-83-596 | Telcordia GR-409Environmental SpaceLow Smoke Zero Halogen (LSZH) | Riser

Flame Test Listing NEC OFCR-ST1 (ETL) and c(ETL)

Flame Test Method | IEC 60332-3 | IEC 60754-2 | IEC 61034-2 | UL 1666 | UL 1685

#### **Environmental Test Specifications**

**Heat Age**  $-20 \,^{\circ}\text{C}$  to  $+85 \,^{\circ}\text{C}$   $(-4 \,^{\circ}\text{F to} +185 \,^{\circ}\text{F})$ 

**Heat Age Test Method** IEC 60794-1 F9

**Low High Bend**  $-10 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (+14  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle** -20 °C to +70 °C (-4 °F to +158 °F)

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

**Cable weight** 136 kg/km | 91.388 lb/kft

#### Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

#### Included Products

CS-5L-TB – LazrSPEED® 300 OM3 Bend-Insensitive Multimode

Fiber

### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

