MCG22HDX13-12-H10



G22HDX Monopole Sector Frame with extended face, 13 ft x 2.88 in OD face pipes. Includes twelve $2.88 \text{ OD} \times 120$ in antenna pipes

Product Classification

Product Type High capacity monopole sector frame

Product Brand PIM-guard

Product Series G2

General Specifications

Mounting Monopole, 381–1270 mm (15–50 in) OD

Pipe, quantity 12
Sectors, quantity 3

Dimensions

Face Width 3.962 m | 13 ft

Width 3,962.4 mm | 156 in

Face Support Pipe Diameter 73.025 mm | 2.875 in

Mounting Diameter, maximum 1270 mm | 50 in

Mounting Diameter, minimum 381 mm | 15 in

 Pipe Outer Diameter
 73.025 mm | 2.875 in

 Stand-off Distance
 1,066.8 mm | 42 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact your local ANDREW representative

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Mounting hardware | Plain end pipes (12) | Ring mounts (2) | Sector frames (3) | Stiff arm

Page 1 of 2



MCG22HDX13-12-H10

Packaging quantity

Weight, net 974.67 kg | 2,148.78 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

