760126235 | P-012-DZ-CM-FSUAQ/8W004 /5L008



Fiber Indoor cable, TeraSPEED® Plenum Distribution, interlocking aluminum armored with plenum jacket, 12 fiber single-unit, Gel-free, Singlemode + Multimode OM3, Feet jacket marking, Aqua jacket color

Product Classification

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East/Africa | North

America

Portfolio CommScope®

Product Type Fiber indoor cable

Product Series P-DZ

General Specifications

Armor Type Interlocking aluminum

Cable Type Distribution

Construction Type Armored

Subunit Type Gel-free

Jacket Color Aqua

Jacket Marking Feet

Composite Fiber Count 4 + 8

Total Fiber Count 12

Dimensions


Diameter Over Armor 10.8 mm | 0.425 in

Diameter Over Jacket 12.8 mm | 0.504 in

Representative Image



760126235 | P-012-DZ-CM-FSUAQ/8W004 /5L008



Mechanical Specifications

Minimum Bend Radius, loaded192 mm7.559 inMinimum Bend Radius, unloaded128 mm5.039 inTensile Load, long term, maximum200 N | 44.962 lbfTensile Load, short term, maximum667 N | 149.948 lbf

 Compression
 85 N/mm | 485.363 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 35 N-m | 309.776 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 136 m | 446.194 ft

Optical Specifications

Fiber Type Composite MM/SM | G.652.D and G.657.A1, TeraSPEED® | OM3, LazrSPEED® 300

Environmental Specifications

Installation temperature 0 °C to +70 °C (+32 °F to +158 °F)

Page 2 of 9

760126235 | P-012-DZ-CM-FSUAQ/8W004 /5L008

Operating Temperature -20 °C to +70 °C (-4 °F to +158 °F)

Storage Temperature $-40 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to} + 158 \,^{\circ}\text{F})$

Cable Qualification StandardsANSI/ICEA S-83-596Telcordia GR-409

Environmental Space Plenum

Flame Test Listing NEC OFCP (ETL) and c(ETL)

Flame Test Method NFPA 130 | NFPA 262

Environmental Test Specifications

Heat Age -20 °C to +85 °C (-4 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-20 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \left(-4 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F}\right)$

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle $-20 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-4 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 151 kg/km | 101.467 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant UK-ROHS Compliant



Included Products

CS-5L-TB – LazrSPEED® 300 OM3 Bend-Insensitive Multimode

Fiber

CS-8W-TB - TeraSPEED® Singlemode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable



LazrSPEED® 300 OM3 Bend-Insensitive Multimode Fiber

LazrSPEED® 300

Product Classification

 Portfolio
 CommScope®

 Product Type
 Optical fiber

General Specifications

Cladding Diameter 125 µm **Cladding Diameter Tolerance** ±5 µm Cladding Non-Circularity, maximum 1 % **Coating Diameter (Colored)** 254 µm **Coating Diameter (Uncolored)** 245 µm **Coating Diameter Tolerance (Colored)** ±7 µm **Coating Diameter Tolerance (Uncolored)** ±10 µm Coating/Cladding Concentricity Error, maximum 12 µm **Core Diameter** 50 µm **Core Diameter Tolerance** ±2.5 µm Core/Clad Offset, maximum $1.5 \, \mu m$

Proof Tensile Stress 100,000 psi (0.69 GPa)

Tight Buffer Diameter 900 μm Tight Buffer Diameter Tolerance $\pm 40 \ \mu m$

Mechanical Specifications

 Macrobending, 15 mm Ø mandrel, 2 turns
 0.20 dB @ 850 nm | 0.50 dB @ 1,300 nm

 Macrobending, 30 mm Ø mandrel, 2 turns
 0.10 dB @ 850 nm | 0.30 dB @ 1,300 nm

 Macrobending, 75 mm Ø mandrel, 100 turns
 0.50 dB @ 1,300 nm | 0.50 dB @ 850 nm

Coating Strip Force, maximum8.9 N | 2.001 lbfCoating Strip Force, minimum1.3 N | 0.292 lbf

Dynamic Fatigue Parameter, minimum 18

COMMSCOPE®

CS-5L-TB

Optical Specifications

Numerical Aperture 0.2

Numerical Aperture Tolerance±0.015Point Defects, maximum0.15 dB

Zero Dispersion Slope, maximum 0.105 ps/[km-nm-nm]

Zero Dispersion Wavelength, maximum 1316 nm **Zero Dispersion Wavelength, minimum** 1297 nm

Optical Specifications, Wavelength Specific

1 Gbps Ethernet Distance 1,020 m @ 850 nm | 600 m @ 1,300 nm

10 Gbps Ethernet Distance 300 m @ 850 nm

Attenuation, maximum 1.00 dB/km @ 1,300 nm | 3.00 dB/km @ 850 nm

Backscatter Coefficient -68.0 dB @ 850 nm | -75.7 dB @ 1,300 nm

 Bandwidth, Laser, minimum
 2,000 MHz-km @ 850 nm | 500 MHz-km @ 1,300 nm

 Bandwidth, OFL, minimum
 1,500 MHz-km @ 850 nm | 500 MHz-km @ 1,300 nm

Differential Mode Delay 0.70 ps/m @ 850 nm

Differential Mode Delay Note Superior to ANSI/TIA TIA-492AAAF and IEC 60793-2-10 at 850 nm

Index of Refraction 1.479 @ 1,300 nm | 1.483 @ 850 nm

Standards Compliance ANSI/TIA-492AAAF (OM3)

Environmental Specifications

Heat Aging, maximum 0.20 dB/km @ 85 °C

Temperature Dependence, maximum0.1 dB/kmTemperature Humidity Cycling, maximum0.2 dB/km

Water Immersion, maximum 0.20 dB/km @ 23 °C

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes

Temperature Dependence, maximum Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

Temperature Humidity Cycling, maximum Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

Page 5 of 9

CS-5L-TB

up to 95% relative humidity



TeraSPEED®

TeraSPEED® Singlemode Fiber

12 µm

Product Classification

 Portfolio
 CommScope®

 Product Type
 Optical fiber

General Specifications

Cladding Diameter125 μmCladding Diameter Tolerance±0.7 μmCladding Non-Circularity, maximum0.7 %Coating Diameter (Colored)249 μmCoating Diameter (Uncolored)242 μmCoating Diameter Tolerance (Colored)±13 μmCoating Diameter Tolerance (Uncolored)±5 μm

Core Diameter 8.3 µm

Proof Tensile Stress 100,000 psi (0.69 GPa)

Tight Buffer Diameter 900 μm Tight Buffer Diameter Tolerance $\pm 40 \ \mu m$

Dimensions

Fiber Curl, minimum 4 m | 13.123 ft

Mechanical Specifications

Coating/Cladding Concentricity Error, maximum

 Macrobending, 20 mm Ø mandrel, 1 turn
 0.75 dB @ 1,550 nm
 | 1.50 dB @ 1,625 nm

 Macrobending, 30 mm Ø mandrel, 10 turns
 0.25 dB @ 1,550 nm
 | 1.00 dB @ 1,625 nm

 Macrobending, 60 mm Ø mandrel, 100 turns
 0.05 dB @ 1,550 nm
 | 0.05 dB @ 1,625 nm

Coating Strip Force, maximum8.9 N | 2.001 lbfCoating Strip Force, minimum1.3 N | 0.292 lbf

COMMSCOPE®

CS-8W-TB

Dynamic Fatigue Parameter, minimum

20

Optical Specifications

Cabled Cutoff Wavelength, maximum1260 nmPoint Defects, maximum0.1 dB

Zero Dispersion Slope, maximum 0.092 ps/[km-nm-nm]

Zero Dispersion Wavelength, maximum1324 nmZero Dispersion Wavelength, minimum1300 nm

Optical Specifications, Wavelength Specific

Attenuation, maximum 0.50 dB/km @ 1,310 nm | 0.50 dB/km @ 1,385

nm | 0.50 dB/km @ 1,490 nm | 0.50 dB/km @ 1,550 nm | 0.50 dB/km @ 1,575 nm | 0.70 dB/km @ 1,270

nm

Backscatter Coefficient -79.6 dB @ 1,310 nm | -82.1 dB @ 1,550 nm

Dispersion, maximum 18 ps(nm-km) at 1550 nm | 3.5 ps(nm-km) from 1285

nm to 1330 nm at 1310 nm

Index of Refraction 1.467 @ 1,310 nm | 1.467 @ 1,385 nm | 1.468 @ 1,550

nm

1,385 nm

Mode Field Diameter Tolerance ±0.4 μm @ 1310 nm | ±0.5 μm @ 1550 nm | ±0.6 μm

@ 1385 nm

Polarization Mode Dispersion Link Design Value, maximum 0.04 ps/sqrt(km)

Standards Compliance | ITU-T G.652.D | ITU-T G.657.A1 | TIA-492CAAB (OS1a)

Environmental Specifications

Heat Aging, maximum 0.05 dB/km @ 85 °C

Temperature Dependence, maximum0.05 dB/kmTemperature Humidity Cycling, maximum0.05 dB/km

Water Immersion, maximum 0.05 dB/km @ 23 °C

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes

COMMSC PE°

CS-8W-TB

Temperature Dependence, maximum

Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

Temperature Humidity Cycling, maximum Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

up to 95% relative humidity

