



Fiber Indoor cable, TeraSPEED® Plenum Distribution, interlocking aluminum armored with plenum jacket, 24 fiber single-unit, Gel-free, Singlemode + Multimode OM3, Feet jacket marking, Aqua jacket color

## Product Classification

|                       |   |
|-----------------------|---|
| Regional Availability | Asia   Australia/New Zealand   Latin America   Middle East/Africa   North America |
| Portfolio             | CommScope®  |
| Product Type          | Fiber indoor cable  |
| Product Series        | P-DZ  |


## General Specifications

|                       |                       |
|-----------------------|-----------------------|
| Armor Type            | Interlocking aluminum |
| Cable Type            | Distribution          |
| Construction Type     | Armored               |
| Subunit Type          | Gel-free              |
| Jacket Color          | Aqua                  |
| Jacket Marking        | Feet                  |
| Composite Fiber Count | 6 + 18                |
| Total Fiber Count     | 24                    |

## Dimensions

|                      |                     |
|----------------------|---------------------|
| Diameter Over Armor  | 13.34 mm   0.525 in |
| Diameter Over Jacket | 17.4 mm   0.685 in  |

## Representative Image



## Mechanical Specifications

|                                   |                                       |
|-----------------------------------|---------------------------------------|
| Minimum Bend Radius, loaded       | 261 mm   10.276 in                    |
| Minimum Bend Radius, unloaded     | 174 mm   6.85 in                      |
| Tensile Load, long term, maximum  | 400 N   89.924 lbf                    |
| Tensile Load, short term, maximum | 1335 N   300.12 lbf                   |
| Compression                       | 85 N/mm   485.363 lb/in               |
| Compression Test Method           | FOTP-41   IEC 60794-1 E3              |
| Flex                              | 25 cycles                             |
| Flex Test Method                  | FOTP-104   IEC 60794-1 E6             |
| Impact                            | 35 N-m   309.776 in lb                |
| Impact Test Method                | FOTP-25   IEC 60794-1 E4              |
| Strain                            | See long and short term tensile loads |
| Strain Test Method                | FOTP-33   IEC 60794-1 E1              |
| Twist                             | 10 cycles                             |
| Twist Test Method                 | FOTP-85   IEC 60794-1 E7              |
| Vertical Rise, maximum            | 133 m   436.352 ft                    |

## Optical Specifications

|            |  |
|------------|--|
| Fiber Type | Composite MM/SM   G.652.D and G.657.A1, TeraSPEED®   OM3, LazrSPEED® 300 |
|------------|--|

## Environmental Specifications

|                          |                                    |
|--------------------------|------------------------------------|
| Installation temperature | 0 °C to +70 °C (+32 °F to +158 °F) |
|--------------------------|------------------------------------|

|                               |                                       |
|-------------------------------|---------------------------------------|
| Operating Temperature         | -20 °C to +70 °C (-4 °F to +158 °F)   |
| Storage Temperature           | -40 °C to +70 °C (-40 °F to +158 °F)  |
| Cable Qualification Standards | ANSI/ICEA S-83-596   Telcordia GR-409 |
| Environmental Space           | Plenum                                |
| Flame Test Listing            | NEC OFCP (ETL) and c(ETL)             |
| Flame Test Method             | NFPA 130   NFPA 262                   |

Environmental Test Specifications

|                               |                                     |
|-------------------------------|-------------------------------------|
| Heat Age                      | -20 °C to +85 °C (-4 °F to +185 °F) |
| Heat Age Test Method          | IEC 60794-1 F9                      |
| Low High Bend                 | -20 °C to +70 °C (-4 °F to +158 °F) |
| Low High Bend Test Method     | FOTP-37   IEC 60794-1 E11           |
| Temperature Cycle             | -20 °C to +70 °C (-4 °F to +158 °F) |
| Temperature Cycle Test Method | FOTP-3   IEC 60794-1 F1             |

Packaging and Weights

|              |                            |
|--------------|----------------------------|
| Cable weight | 307 kg/km   206.294 lb/kft |
|--------------|----------------------------|

Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

Included Products

|          |   |
|----------|---|
| CS-5L-TB | – LazrSPEED® 300 OM3 Bend-Insensitive Multimode Fiber |
| CS-8W-TB | – TeraSPEED® Singlemode Fiber                         |

\* Footnotes

|                       |   |
|-----------------------|---|
| Operating Temperature | Specification applicable to non-terminated bulk fiber cable |
|-----------------------|---|