SSH-114-3



SnapStak® Hanger for 1-1/4 in coaxial cable, triple stack capability, includes reinforcement bar

Product Classification

Product Type	Hanger kit
Product Brand	SnapStak®
Ordering Note	ANDREW® non-standard product
General Specifications	
Cables per Hanger	1
Color	Silver
Hanger Type	Snap-in hanger
Mounting	3/4 in drilled cable ladder
Dimensions	

Maximum Stack Height 3 Height 40.9 mm | 1.61 in Width 40.1 mm | 1.579 in Length 81 mm | 3.189 in 37.6-43.2 mm **Compatible Cable Diameter Range Compatible Diameter, maximum** 43.2 mm | 1.701 in **Compatible Diameter, minimum** 37.6 mm | 1.48 in Nominal Size 1-1/4 in **Electrical Specifications Return Loss Effect, maximum** 0.1 dB DTF Effect, maximum 0.1 dB

Material Specifications

Material Type

Mechanical Specifications

Page 1 of 4



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 3, 2025

Stainless steel

SSH-114-3

Vibration Survival

≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Corrosion Resistance, minimum with no degredation	≥500 hours in salt spray chamber
Environmental Strength Capability	Double cable weight
Packaging and Weights	
Height, packed	22 cm 8.661 in
Width, packed	14.6 cm 5.748 in
Length, packed	14.8 cm 5.827 in
Packaging quantity	10

Weight, gross

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

Included Products

SSHR-10

SnapStak Hanger Reinforcement Bar, PIM free bar provides the ability to add an additional cable run to the stack

0.52 kg | 1.146 lb

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power

Page 2 of 4

SSHR-10



SnapStak Hanger Reinforcement Bar, PIM free bar provides the ability to add an additional cable run to the stack

Product Classification Product Type Adapter Product Brand SnapStak® **Ordering Note** ANDREW® standard product in the United States and Canada General Specifications Accessories Adapters Color Black 3/4 in through hole Mounting Dimensions Height 76.2 mm | 3 in Width 25.4 mm | 1 in Length 6.35 mm | 0.25 in Material Specifications Material Type Engineered plastic Mechanical Specifications Maximum Loading Quadruple stack for SSH-M | Triple stack for hangers SSH-XL, SSH-L | Triple stack, 1-5/8 in cable Vibration Survival ≥4 hours at resonant frequency **Environmental Specifications Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F) UV Resistance, minimum with no degradation ≥1000 hours exposure in accelerated UV life chamber Packaging and Weights Height, packed 17 cm | 6.693 in

Page 3 of 4



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 3, 2025

SSHR-10

Width, packed	13 cm 5.118 in
Length, packed	10 cm 3.937 in
Packaging quantity	10
Weight, gross	0.15 kg 0.331 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Page 4 of 4



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 3, 2025