



FACT® Fiber Optic High Density Patch Chassis, gray, 4E high, 144-port, singlemode, holding 8 hinged trays (2 per Element) loaded with SC adapterpacks

- Designed for use with the all-purpose all-front-access FACT frames and FIST-GR3 frames supporting up to 2,688 LC or 1,344 SC connections in a single frame (FACT-IC frame 2880 LC or 1440 SC)
- Reduced installation and maintenance time via the toolless snap-on design supporting both interconnect and cross-connect applications
- Flexible customization enabled by 4 chassis types (patch-only, patch-splice, pre-cabled and splice-only) to support all ODF applications
- High density through the single FACT element height (1E) being 30% less tall compared to the industry standard panel height (1HU)

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber patch chassis
Product Brand	FACT®
Product Series	FACT

## General Specifications


Functionality	Patching
Application	Compatible with FACT frames   Compatible with FIST-GR3-R frames when backplate is used (optional)
Body Style	Symmetrical
Color	Gray
Growth Configuration	Fully loaded
Interface, front	SC/APC
Patch Cord Routing	Left sided   Right sided
Rack Type	FACT
Rack Units	2.8
Shelf Movement	Sliding
Total Ports, quantity	144
Transmission Standards	ETSI EN 300 019-1-3   IEC 61300-3-30

# 760253216 | FACT-4EPATHDSC

## Dimensions

Height	123.8 mm   4.874 in
Width	524 mm   20.63 in
Depth	283 mm   11.142 in

## Ordering Tree



## Optical Specifications

Fiber Mode	Singlemode
------------	------------

## Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-20 °C to +85 °C (-4 °F to +176 °F)
Flammability Rating	UL 94 V-0

## Packaging and Weights

Included	Mounting hardware for FACT frame
Packaging quantity	1