



IFEB40, Indoor Fiber Optic Wall mount Enclosure, Splice / Patch, LC/APC Pigtails and Adapters (96),Single Elemet Slim trays(24) Smouv, Feeder Cable Seal 4x15mm and 24x7mm drop seal(2), RAL 9010

- Compact, wall mountable fiber enclosures for indoor use
- Specifically designed for fast FTTH deployment and easy customer connection
- Configurable as splice only or connectorized solution
- Multiple and modular wrap around cable port sealing options to suit a wide range of cables
- Easy intergration of 900µm connectorised or 250µm splice splitters
- Single Element (SE), Single Slim Element (SLE) or Single Circuit (SC) tray options - Smouv and ANT
- Powered by NOVUX™

Product Classification

Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Fiber wall box
Product Series	IFEB-40

General Specifications

Functionality	Patching   Splicing
Access	Front
Adapter Ports, quantity	96
Cable Ports, quantity	4
Drop Port, quantity	48
Enclosure Color	Pure White (RAL 9010)
Front Cover Type	Snap-on cover
Interface	LC/APC
Pigtails Included, quantity	96
Splice Tray Construction	SLE (Slim element tray for up to 12 primary coated fibers)
Splicing Capacity, maximum	288
Splicing Type	SMOUV


Dimensions

Height	425 mm   16.732 in
--------	--------------------

# 760259800 | IFEB-40WB4096C24SGJJNN000


Height, with cover	500 mm   19.685 in
Width	295 mm   11.614 in
Depth	145 mm   5.709 in

## Dimension Drawing



## Ordering Tree

# 760259800 | IFEB-40WB4096C24SGJJNN000



## Environmental Specifications

Installation temperature	-5 °C to +45 °C (+23 °F to +113 °F)
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Environmental Space	Indoor
Flammability Rating	UL 94 V-0
Qualification Standards	IEC 60529, IP50   IEC 61753-1 Ed.2 2018 - Category C

## Packaging and Weights

Included	Adapters (24)   Box (1)   Drop Seal, 24x7 (2)   Feeder Seal, 4x15 (1)   SLE Smouv trays (24)
Packaging quantity	1
Packaging Type	Box

## Regulatory Compliance/Certifications

Agency

CHINA-ROHS  
ROHS  
UK-ROHS

Classification

Above maximum concentration value  
Compliant/Exempted  
Compliant/Exempted

