760134718 | R-036-LZ-CM-F12BK/25D/8W012 /5K024



Fiber indoor/outdoor cable, TeraSPEED® Riser Rated, Gel-Free, 36 fiber, Multimode/Singlemode, Stranded Loose Tube with Aluminum Interlocking Armor containing a Riser Rated Outer Jacket, Black jacket color, Feet cable marking

Product Classification

Regional Availability	Asia Australia/New Zealand Latin America Middle East /Africa North America	
Portfolio	CommScope®	
Product Type	Fiber indoor/outdoor cable	
Product Series	R-LZ	
General Specifications		
Armor Type	Interlocking aluminum	
Cable Type	Stranded loose tube	
Construction Type	Armored	
Subunit Type	Gel-free	
Filler, quantity	2	
Jacket Color	Black	
Jacket Marking	Feet	
Subunit, quantity	3	
Fibers per Subunit, quantity	12	
Composite Fiber Count	12 + 24	
Total Fiber Count	36	
Dimensions		
Buffer Tube/Subunit Diameter	2.5 mm 0.098 in	
Diameter Over Armor	18.4 mm 0.724 in	
Diameter Over Jacket	20.5 mm 0.807 in	


Representative Image

Page 1 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 1, 2025



760134718 | R-036-LZ-CM-F12BK/25D/8W012 /5K024



Mechanical Specifications

Minimum Bend Radius, loaded	409 mm 16.102 in
Minimum Bend Radius, unloaded	286 mm 11.26 in
Tensile Load, long term, maximum	400 N 89.924 lbf
Tensile Load, short term, maximum	1335 N 300.12 lbf
Compression	85 N/mm 485.363 lb/in
Compression Test Method	FOTP-41 IEC 60794-1 E3
Flex	25 cycles
Flex Test Method	FOTP-104 IEC 60794-1 E6
Impact	35 N-m 309.776 in lb
Impact Test Method	FOTP-25 IEC 60794-1 E4
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33 IEC 60794-1 E1
Twist	10 cycles
Twist Test Method	FOTP-85 IEC 60794-1 E7
Vertical Rise, maximum	125 m 410.105 ft
Optical Specifications	
Fiber Type	Composite MM/SM G.652.D and G.657.A1, TeraSPEED® OM4,

LazrSPEED® 550 | OS2 | OS2

Environmental Specifications

Installation temperature

Operating Temperature

-10 °C to +60 °C (+14 °F to +140 °F) -40 °C to +70 °C (-40 °F to +158 °F)

Page 2 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 1, 2025



760134718 | R-036-LZ-CM-F12BK/25D/8W012

Storage Temperature	-40 °C to +75 °C (-40 °F to +167 °F)	
Cable Qualification Standards	ANSI/ICEA S-104-696 EN 187105 Telcordia GR-409	
Environmental Space	Riser	
Flame Test Listing	NEC OFCR (ETL) and c(ETL)	
Flame Test Method	UL 1666	
Jacket UV Resistance	UV stabilized	
Water Penetration	24 h	
Water Penetration Test Method	FOTP-82 IEC 60794-1 F5	

Environmental Test Specifications

Cable Freeze	-2 °C 28.4 °F
Cable Freeze Test Method	FOTP-98 IEC 60794-1 F15
Heat Age	-40 °C to +85 °C (-40 °F to +185 °F)
Heat Age Test Method	IEC 60794-1 F9
Low High Bend	-30 °C to +60 °C (-22 °F to +140 °F)
Low High Bend Test Method	FOTP-37 IEC 60794-1 E11
Temperature Cycle	-40 °C to +70 °C (-40 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3 IEC 60794-1 F1

Packaging and Weights

Cable weight

/5K024

320 kg/km | 215.03 lb/kft

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

Included Products

CS-5K-LT – LazrSPEED® 550 OM4 Bend-Insensitive Multimode Fiber CS-8W-IOLT – TeraSPEED® OS2 Singlemode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

Page 3 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 1, 2025

