760146076 | P-001-SP-8W-F160R



Fiber indoor cable, TeraSPEED® 1.6 mm Plenum, 1 fiber, Singlemode G. 652.D and G.657.A1, Feet jacket marking, Orange jacket color

Product Classification

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East/Africa | North

America

Portfolio CommScope®

Product Type Fiber indoor cable

Product Series P-SP

General Specifications

Cable TypeCordage

Construction Type Non-armored

Subunit Type Gel-free

Jacket Color Orange

Jacket Marking Feet

Total Fiber Count 1


Dimensions

Diameter Over Jacket 1.7 mm | 0.067 in

Representative Image



760146076 | P-001-SP-8W-F160R



Mechanical Specifications

Minimum Bend Radius, loaded38 mm1.496 inMinimum Bend Radius, unloaded15 mm0.591 inTensile Load, long term, maximum29 N | 6.519 lbfTensile Load, short term, maximum98 N | 22.031 lbf

Compression 10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 0.74 N-m | 6.55 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 500 m | 1,640.42 ft

Optical Specifications

Fiber Type G.652.D and G.657.A1, TeraSPEED®

Environmental Specifications



760146076 | P-001-SP-8W-F160R

Installation temperature $0 \, ^{\circ}\text{C}$ to +70 $^{\circ}\text{C}$ (+32 $^{\circ}\text{F}$ to +158 $^{\circ}\text{F}$)

Operating Temperature $-20 \, ^{\circ}\text{C}$ to +70 $^{\circ}\text{C}$ (-4 $^{\circ}\text{F}$ to +158 $^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

Environmental Space Plenum

Flame Test Listing NEC OFNP (ETL) and c(ETL)

Flame Test Method NFPA 130 | NFPA 262

Environmental Test Specifications

Heat Age $-20 \, ^{\circ}\text{C} \text{ to } +85 \, ^{\circ}\text{C} \, (-4 \, ^{\circ}\text{F to } +185 \, ^{\circ}\text{F})$

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-20 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-4 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle -20 °C to +70 °C (-4 °F to +158 °F)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 3 kg/km | 2.016 lb/kft

Included Products

CS-8W-TB - TeraSPEED® Singlemode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

