

Fiber Optic Drop Cable Assembly, SC/APC to SC/APC, USD dielectric cable

- Hardened connectors are factory-terminated and environmentally sealed for use in optical drop cable deployments
- Hardened drop cables incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Hardened drop cables simplify installation and maintenance by reducing splicing requirements in the distribution portion of the network
- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability	Latin America North America
Product Type	Fiber drop cable assembly
Product Brand	PRODIGY™
Product Series	HCA
Government Requirements	Build America Buy America (BABA) compliant*

General Specifications


Cable Type	Dielectric - Universal Flat
Connector A, quantity	1
Color, boot A	Green
Color, connector A	Green
Connector B, quantity	1
Color, boot B	Green
Color, connector B	Green
Interface, Connector A	SC/APC with pulling sock
Interface, Connector B	SC/APC with pulling sock
Jacket Color	Black
Location of Manufacturing	Catawba, North Carolina
Total Fibers, quantity	1
Transmission Standards	IEC 61753-1 IEC 61754-4 IEC 61755

Dimensions


HCA-LL1C

Breakout Length, connector A	609.6 mm 24 in
Breakout Length, connector B	609.6 mm 24 in
Cable Assembly Length Range (m)	1 – 900
Cable Assembly Length Range (ft)	1 – 2500
Cable Outer Diameter	4.6 x 8.0 mm (0.18 x 0.31 in)

Ordering Tree



Representative Image



Mechanical Specifications

Minimum Bend Radius, loaded	92 mm 3.622 in
Minimum Bend Radius, unloaded	64 mm 2.52 in
Tensile Load, long term, maximum	400 N 89.924 lbf
Tensile Load, short term, maximum	1334 N 299.895 lbf
Cable Crush Resistance, maximum	44 N/mm 251.246 lb/in
Pulling Tension, maximum	11.34 kg 25 lb

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2, TeraSPEED®
Insertion Loss, maximum, connector A	0.4 dB
Insertion Loss, maximum, connector B	0.4 dB
Return Loss, minimum, connector A	65 dB
Return Loss, minimum, connector B	65 dB

Environmental Specifications

Installation temperature	-30 °C to +60 °C (-22 °F to +140 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +75 °C (-40 °F to +167 °F)
Environmental Space	Outdoor
Jacket UV Resistance	UV stabilized

HCA-LL1C

Qualification Standards	NEMA type 6, 10 ft waterhead Telcordia GR-20 Telcordia GR-3120
Packaging and Weights	
Cable weight	34.4 kg/km 23.116 lb/kft
Packaging quantity	1