



Fiber indoor/outdoor cable, LazrSPEED® Zero Halogen Riser Distribution, 2 fiber single-unit, Multimode OM3, Feet jacket marking, Black jacket color, Dca flame rating

Product Classification

|                       |   |
|-----------------------|---|
| Regional Availability | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| Portfolio             | CommScope®  |
| Product Type          | Fiber indoor/outdoor cable  |
| Product Series        | Z-DS  |

General Specifications

|                   |              |
|-------------------|--------------|
| Cable Type        | Distribution |
| Construction Type | Non-armored  |
| Jacket Color      | Black        |
| Jacket Marking    | Feet         |
| Total Fiber Count | 2            |

Dimensions

|                      |                  |
|----------------------|------------------|
| Diameter Over Jacket | 3.8 mm   0.15 in |
|----------------------|------------------|

Representative Image



## Mechanical Specifications

|                                   |                                       |
|-----------------------------------|---------------------------------------|
| Minimum Bend Radius, loaded       | 58 mm   2.283 in                      |
| Minimum Bend Radius, unloaded     | 38 mm   1.496 in                      |
| Tensile Load, long term, maximum  | 300 N   67.443 lbf                    |
| Tensile Load, short term, maximum | 1000 N   224.809 lbf                  |
| Compression                       | 10 N/mm   57.101 lb/in                |
| Compression Test Method           | FOTP-41   IEC 60794-1 E3              |
| Flex                              | 100 cycles                            |
| Flex Test Method                  | FOTP-104   IEC 60794-1 E6             |
| Impact                            | 2.94 N-m   26.021 in lb               |
| Impact Test Method                | FOTP-25   IEC 60794-1 E4              |
| Strain                            | See long and short term tensile loads |
| Strain Test Method                | FOTP-33   IEC 60794-1 E1              |
| Twist                             | 10 cycles                             |
| Twist Test Method                 | FOTP-85   IEC 60794-1 E7              |
| Vertical Rise, maximum            | 500 m   1,640.42 ft                   |

## Optical Specifications

|            |   |
|------------|---|
| Fiber Type | OM3, LazrSPEED® 300   OM3, LazrSPEED® 300 |
|------------|---|

## Environmental Specifications

|                          |                                      |
|--------------------------|--------------------------------------|
| Installation temperature | -30 °C to +60 °C (-22 °F to +140 °F) |
|--------------------------|--------------------------------------|

# 760143198 | Z-002-DS-5L-FSUBK/D

|   |  |
|---|--|
| <b>Operating Temperature</b>                        | -40 °C to +70 °C (-40 °F to +158 °F)   |
| <b>Storage Temperature</b>                          | -40 °C to +75 °C (-40 °F to +167 °F)   |
| <b>Cable Qualification Standards</b>                | ANSI/ICEA S-104-696   EN 187105   Telcordia GR-20 (water penetration)   Telcordia GR-409 |
| <b>EN50575 CPR Cable EuroClass Fire Performance</b> | Dca  |
| <b>EN50575 CPR Cable EuroClass Smoke Rating</b>     | s1a  |
| <b>EN50575 CPR Cable EuroClass Droplets Rating</b>  | d1   |
| <b>EN50575 CPR Cable EuroClass Acidity Rating</b>   | a2   |
| <b>Environmental Space</b>                          | Low Smoke Zero Halogen (LSZH)   Riser  |
| <b>Flame Test Listing</b>                           | NEC OFNR-ST1 (ETL) and c(ETL)  |
| <b>Flame Test Method</b>                            | IEC 60332-3   IEC 60754-2   IEC 61034-2   UL 1666   UL 1685                              |
| <b>Jacket UV Resistance</b>                         | UV stabilized  |
| <b>Water Penetration</b>                            | 24 h   |
| <b>Water Penetration Test Method</b>                | FOTP-82   IEC 60794-1 F5   |

## Environmental Test Specifications

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| <b>Cable Freeze Test Method</b>      | IEC 60794-1 F15                      |
| <b>Heat Age</b>                      | -40 °C to +85 °C (-40 °F to +185 °F) |
| <b>Heat Age Test Method</b>          | IEC 60794-1 F9                       |
| <b>Low High Bend</b>                 | -40 °C to +70 °C (-40 °F to +158 °F) |
| <b>Low High Bend Test Method</b>     | FOTP-37   IEC 60794-1 E11            |
| <b>Temperature Cycle</b>             | -40 °C to +70 °C (-40 °F to +158 °F) |
| <b>Temperature Cycle Test Method</b> | FOTP-3   IEC 60794-1 F1              |

## Packaging and Weights

|                     |                           |
|---------------------|---------------------------|
| <b>Cable weight</b> | 11.6 kg/km   7.795 lb/kft |
|---------------------|---------------------------|

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CENELEC       | EN 50575 compliant, Declaration of Performance (DoP) available   |
| CHINA-ROHS    | Below maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |



## Included Products

CS-5L-TB – LazrSPEED® 300 OM3 Bend-Insensitive Multimode Fiber

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

## LazrSPEED® 300 OM3 Bend-Insensitive Multimode Fiber

### LazrSPEED® 300

#### Product Classification

|              |               |
|--------------|---------------|
| Portfolio    | CommScope®    |
| Product Type | Optical fiber |

#### General Specifications

|   |                        |
|---|------------------------|
| Cladding Diameter                             | 125 µm                 |
| Cladding Diameter Tolerance                   | ±5 µm                  |
| Cladding Non-Circularity, maximum             | 1 %                    |
| Coating Diameter (Colored)                    | 254 µm                 |
| Coating Diameter (Uncolored)                  | 245 µm                 |
| Coating Diameter Tolerance (Colored)          | ±7 µm                  |
| Coating Diameter Tolerance (Uncolored)        | ±10 µm                 |
| Coating/Cladding Concentricity Error, maximum | 12 µm                  |
| Core Diameter                                 | 50 µm                  |
| Core Diameter Tolerance                       | ±2.5 µm                |
| Core/Clad Offset, maximum                     | 1.5 µm                 |
| Proof Tensile Stress                          | 100,000 psi (0.69 GPa) |
| Tight Buffer Diameter                         | 900 µm                 |
| Tight Buffer Diameter Tolerance               | ±40 µm                 |

#### Mechanical Specifications

|  |                                       |
|--|---------------------------------------|
| Macrobending, 15 mm Ø mandrel, 2 turns   | 0.20 dB @ 850 nm   0.50 dB @ 1,300 nm |
| Macrobending, 30 mm Ø mandrel, 2 turns   | 0.10 dB @ 850 nm   0.30 dB @ 1,300 nm |
| Macrobending, 75 mm Ø mandrel, 100 turns | 0.50 dB @ 1,300 nm   0.50 dB @ 850 nm |
| Coating Strip Force, maximum             | 8.9 N   2.001 lbf                     |
| Coating Strip Force, minimum             | 1.3 N   0.292 lbf                     |
| Dynamic Fatigue Parameter, minimum       | 18                                    |

# CS-5L-TB

## Optical Specifications

|                                     |                     |
|-------------------------------------|---------------------|
| Numerical Aperture                  | 0.2                 |
| Numerical Aperture Tolerance        | ±0.015              |
| Point Defects, maximum              | 0.15 dB             |
| Zero Dispersion Slope, maximum      | 0.105 ps/[km-nm-nm] |
| Zero Dispersion Wavelength, maximum | 1316 nm             |
| Zero Dispersion Wavelength, minimum | 1297 nm             |

## Optical Specifications, Wavelength Specific

|                              |   |
|------------------------------|---|
| 1 Gbps Ethernet Distance     | 1,020 m @ 850 nm   600 m @ 1,300 nm                           |
| 10 Gbps Ethernet Distance    | 300 m @ 850 nm  |
| Attenuation, maximum         | 1.00 dB/km @ 1,300 nm   3.00 dB/km @ 850 nm                   |
| Backscatter Coefficient      | -68.0 dB @ 850 nm   -75.7 dB @ 1,300 nm                       |
| Bandwidth, Laser, minimum    | 2,000 MHz-km @ 850 nm   500 MHz-km @ 1,300 nm                 |
| Bandwidth, OFL, minimum      | 1,500 MHz-km @ 850 nm   500 MHz-km @ 1,300 nm                 |
| Differential Mode Delay      | 0.70 ps/m @ 850 nm  |
| Differential Mode Delay Note | Superior to ANSI/TIA TIA-492AAAF and IEC 60793-2-10 at 850 nm |
| Index of Refraction          | 1.479 @ 1,300 nm   1.483 @ 850 nm                             |
| Standards Compliance         | ANSI/TIA-492AAAF (OM3)  |

## Environmental Specifications

|                                       |                    |
|---------------------------------------|--------------------|
| Heat Aging, maximum                   | 0.20 dB/km @ 85 °C |
| Temperature Dependence, maximum       | 0.1 dB/km          |
| Temperature Humidity Cycling, maximum | 0.2 dB/km          |
| Water Immersion, maximum              | 0.20 dB/km @ 23 °C |

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

## \* Footnotes

|                                       |   |
|---------------------------------------|---|
| Temperature Dependence, maximum       | Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)       |
| Temperature Humidity Cycling, maximum | Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F) |

# CS-5L-TB

---

up to 95% relative humidity