

# PREMIUM Certificate

no. c6168k-20

## Customer:

CommScope INC.  
3642 US-70  
Claremont, NC 28610-0879, USA

VALID TO DECEMBER 2025

## Category 6A

## Test sample(s):

Balanced cord:

**NETCONNECT Patch Cord NPC Cat.6A LSZH S/FTP AWG26**

Part-no.: NPC6ASZDB-WTXXM (white); NPC6ASZDB-BLXXM (blue);  
NPC6ASZDB-GYXXM (gray); NPC6ASZDB-GNXXM (green);  
NPC6ASZDB-ORXXM (orange); NPC6ASZDB-RDXXM (red);  
NPC6ASZDB-YLXXM (yellow); NPC6ASZDB-BKXXM (black)

## Applied standard(s):

ISO/IEC 11801-1 Ed.1.0 (2017-11)  
DIN EN 50173-1 (2018-10)  
IEC 61935-2 Ed.3.0 (2010-07)

## Result(s):

The sample meets the limits of the applied standards and regulations with respect to the parameters indicated above.

## Balanced cord, copper, Category 6A

## GHMT PREMIUM Verification Program, GHMT PVP

Ongoing compliance with the specifications is monitored within the framework of regular sampling, which cannot be influenced by the customer, thus defining high standards as regards continuous manufacturing quality.

This Certificate refers to the comprehensive test report no. **R6168k-20** and shall only be applicable in conjunction with the test report.

Bexbach, 03.06.2025



Dirk Wilhelm, engineer  
(Chairman of the Managing Board)



*Test laboratory accredited by DAkkS in accordance with DIN EN ISO/IEC 17025:2018.  
The accreditation is valid for the test methods listed in certificate D-PL-17559-01-00.*

## GHMT AG

In der Kolling 320  
66450 Bexbach / Germany

PO box 11 16  
66442 Bexbach / Germany

T: +49 6826 92 28-0  
F: +49 6826 92 28-290

info@ghmt.de  
www.ghmt.de

**RELIABILITY IN TOTAL  
REQUIRES ACCURACY IN DETAIL.**