



Fiber indoor/outdoor cable, LazrSPEED®, Single Jacket/Single Armor, Low Smoke Zero Halogen (LSZH), Gel-Free, 144 fiber, Stranded Loose Tube, Multimode OM3, Black jacket color, Feet jacket marking, Cca flame rating

- Corrugated steel tape armor is strong yet flexible, providing additional crush and rodent protection

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Europe   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber indoor/outdoor cable
Product Series	Z-LA

## General Specifications

Armor Type	Corrugated steel
Cable Type	Stranded loose tube
Construction Type	Armored
Subunit Type	Gel-free
Filler, quantity	0
Jacket Color	Black
Jacket Marking	Feet
Subunit, quantity	12
Fibers per Subunit, quantity	12
Total Fiber Count	144

## Dimensions

Buffer Tube/Subunit Diameter	2.5 mm   0.098 in
Diameter Over Jacket	18.7 mm   0.736 in

## Representative Image



## Mechanical Specifications

Minimum Bend Radius, loaded	280 mm   11.024 in
Minimum Bend Radius, unloaded	187 mm   7.362 in
Tensile Load, long term, maximum	800 N   179.847 lbf
Tensile Load, short term, maximum	2700 N   606.984 lbf
Compression	44 N/mm   251.246 lb/in
Compression Test Method	FOTP-41   IEC 60794-1 E3
Flex	25 cycles
Flex Test Method	FOTP-104   IEC 60794-1 E6
Impact	5.15 N-m   45.581 in lb
Impact Test Method	FOTP-25   IEC 60794-1 E4
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33   IEC 60794-1 E1
Twist	10 cycles
Twist Test Method	FOTP-85   IEC 60794-1 E7
Vertical Rise, maximum	229 m   751.312 ft

## Optical Specifications

Fiber Type	OM3, LazrSPEED® 300   OM3, LazrSPEED® 300
------------	---

## Environmental Specifications

Installation temperature	-30 °C to +60 °C (-22 °F to +140 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

# 760155085 | Z-144-LA-5L-F12BK/25D/C

Storage Temperature	-40 °C to +75 °C (-40 °F to +167 °F)
Cable Qualification Standards	ANSI/ICEA S-104-696   EN 187105   Telcordia GR-20   Telcordia GR-409
EN50575 CPR Cable EuroClass Fire Performance	Cca
EN50575 CPR Cable EuroClass Smoke Rating	s1b
EN50575 CPR Cable EuroClass Droplets Rating	d2
EN50575 CPR Cable EuroClass Acidity Rating	a1
Environmental Space	Aerial, lashed   Buried   Low Smoke Zero Halogen (LSZH)
Flame Test Listing	EN 50399   NEC OFC-ST1 (ETL) and c(ETL)
Flame Test Method	CSA FT4   EN 50399   IEC 60332-3   IEC 60754-2   IEC 61034-2   IEEE 1202   NES 713   UL 1685
Jacket UV Resistance	UV stabilized
Water Penetration	24 h
Water Penetration Test Method	FOTP-82   IEC 60794-1 F5

## Environmental Test Specifications

Cable Freeze	-2 °C   28.4 °F
Cable Freeze Test Method	FOTP-98   IEC 60794-1 F15
Heat Age	-40 °C to +85 °C (-40 °F to +185 °F)
Heat Age Test Method	IEC 60794-1 F9
Low High Bend	-30 °C to +60 °C (-22 °F to +140 °F)
Low High Bend Test Method	FOTP-37   IEC 60794-1 E11
Temperature Cycle	-40 °C to +70 °C (-40 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3   IEC 60794-1 F1

## Packaging and Weights

Cable weight	357 kg/km   239.893 lb/kft
--------------	----------------------------

## Regulatory Compliance/Certifications

Agency	Classification
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## Included Products

# 760155085 | Z-144-LA-5L-F12BK/25D/C

---

CS-5L-LT – LazrSPEED® 300 OM3 Bend-Insensitive Multimode Fiber

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

LazrSPEED® 300 OM3 Bend-Insensitive Multimode Fiber

LazrSPEED® 300

Product Classification

Portfolio	CommScope®
Product Type	Optical fiber

General Specifications

Cladding Diameter	125 µm
Cladding Diameter Tolerance	±5 µm
Cladding Non-Circularity, maximum	1 %
Coating Diameter (Colored)	254 µm
Coating Diameter (Uncolored)	245 µm
Coating Diameter Tolerance (Colored)	±7 µm
Coating Diameter Tolerance (Uncolored)	±10 µm
Coating/Cladding Concentricity Error, maximum	12 µm
Core Diameter	50 µm
Core Diameter Tolerance	±2.5 µm
Core/Clad Offset, maximum	1.5 µm
Proof Tensile Stress	100,000 psi (0.69 GPa)

Mechanical Specifications

Macrobending, 15 mm Ø mandrel, 2 turns	0.20 dB @ 850 nm   0.50 dB @ 1,300 nm
Macrobending, 30 mm Ø mandrel, 2 turns	0.10 dB @ 850 nm   0.30 dB @ 1,300 nm
Macrobending, 75 mm Ø mandrel, 100 turns	0.50 dB @ 1,300 nm   0.50 dB @ 850 nm
Coating Strip Force, maximum	8.9 N   2.001 lbf
Coating Strip Force, minimum	1.3 N   0.292 lbf
Dynamic Fatigue Parameter, minimum	18

Optical Specifications

Numerical Aperture	0.2
--------------------	-----

# CS-5L-LT

Numerical Aperture Tolerance	±0.015
Point Defects, maximum	0.15 dB
Zero Dispersion Slope, maximum	0.105 ps/[km-nm-nm]
Zero Dispersion Wavelength, maximum	1316 nm
Zero Dispersion Wavelength, minimum	1297 nm

## Optical Specifications, Wavelength Specific

1 Gbps Ethernet Distance	1,020 m @ 850 nm   600 m @ 1,300 nm
10 Gbps Ethernet Distance	300 m @ 850 nm
Attenuation, maximum	1.00 dB/km @ 1,300 nm   3.00 dB/km @ 850 nm
Backscatter Coefficient	-68.0 dB @ 850 nm   -75.7 dB @ 1,300 nm
Bandwidth, Laser, minimum	2,000 MHz-km @ 850 nm   500 MHz-km @ 1,300 nm
Bandwidth, OFL, minimum	1,500 MHz-km @ 850 nm   500 MHz-km @ 1,300 nm
Differential Mode Delay	0.70 ps/m @ 850 nm
Differential Mode Delay Note	Superior to ANSI/TIA TIA-492AAAF and IEC 60793-2-10 at 850 nm
Index of Refraction	1.479 @ 1,300 nm   1.483 @ 850 nm
Standards Compliance	ANSI/TIA-492AAAF (OM3)

## Environmental Specifications

Heat Aging, maximum	0.20 dB/km @ 85 °C
Temperature Dependence, maximum	0.1 dB/km
Temperature Humidity Cycling, maximum	0.2 dB/km
Water Immersion, maximum	0.20 dB/km @ 23 °C

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

## \* Footnotes

Temperature Dependence, maximum	Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)
Temperature Humidity Cycling, maximum	Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F) up to 95% relative humidity