

Fiber indoor/outdoor cable, TeraSPEED®, Single Jacket/Single Armor, Low Smoke Zero Halogen (LSZH), 12 fiber, Singlemode G.652.D and G. 657.A1, Gel-Free, Stranded Loose Tube, Black jacket color, Feet jacket marking, Cca flame rating

 Corrugated steel tape armor is strong yet flexible, providing additional crush and rodent protection

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Europe | Latin

America | North America

Portfolio CommScope®

Product Type Fiber indoor/outdoor cable

Product Series Z-LA

General Specifications

Armor Type Corrugated steel

Cable Type Stranded loose tube

Construction TypeArmoredSubunit TypeGel-free

Filler, quantity 4

Jacket Color Black
Jacket Marking Feet

Subunit, quantity 1

Fibers per Subunit, quantity 12


Total Fiber Count 12

Dimensions

Buffer Tube/Subunit Diameter2.5 mm | 0.098 inDiameter Over Jacket13 mm | 0.512 in

Representative Image





Mechanical Specifications

Minimum Bend Radius, loaded195 mm7.677 inMinimum Bend Radius, unloaded130 mm5.118 inTensile Load, long term, maximum800 N | 179.847 lbf

Tensile Load, short term, maximum 2700 N | 606.984 lbf

 Compression
 22 N/mm | 125.623 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 3 N-m | 26.552 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 461 m | 1,512.467 ft

Optical Specifications

Fiber Type G.652.D and G.657.A1, TeraSPEED® | OS2 | OS2

Environmental Specifications

Installation temperature $-30 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-22 $^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

COMMSCOPE®

Storage Temperature -40 °C to +75 °C (-40 °F to +167 °F)

Cable Qualification Standards ANSI/ICEA S-104-696 | EN 187105 | Telcordia GR-20 | Telcordia GR-

409

EN50575 CPR Cable EuroClass Fire PerformanceCcaEN50575 CPR Cable EuroClass Smoke Ratings1bEN50575 CPR Cable EuroClass Droplets Ratingd2EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Aerial, lashed | Buried | Low Smoke Zero Halogen (LSZH)

Flame Test Listing EN 50399 | NEC OFC-ST1 (ETL) and c(ETL)

Flame Test Method EN 50399 | IEC 60332-3 | IEC 60754-2 | IEC 61034-2 | IEEE

1202 | UL 1685

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method FOTP-82 | IEC 60794-1 F5

Environmental Test Specifications

Cable Freeze -2 °C | 28.4 °F

Cable Freeze Test Method FOTP-98 | IEC 60794-1 F15

Heat Age -40 °C to +85 °C (-40 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-30 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-22 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle -40 °C to +70 °C (-40 °F to +158 °F)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 177 kg/km | 118.939 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



UK-ROHS

Compliant



Included Products

CS-8W-IOLT - TeraSPEED® OS2 Singlemode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable



TeraSPEED® OS2 Singlemode Fiber

 $0.5 \, \mu m$

TeraSPEED®

Product Classification

 Portfolio
 CommScope®

 Product Type
 Optical fiber

General Specifications

Cladding Diameter 125 µm **Cladding Diameter Tolerance** $\pm 0.7 \, \mu m$ 0.7 % Cladding Non-Circularity, maximum **Coating Diameter (Colored)** 249 µm **Coating Diameter (Uncolored)** $242 \, \mu m$ **Coating Diameter Tolerance (Colored)** ±13 µm **Coating Diameter Tolerance (Uncolored)** ±5 µm Coating/Cladding Concentricity Error, maximum 12 µm **Core Diameter** 8.3 µm

Proof Tensile Stress 100,000 psi (0.69 GPa)

Dimensions

Core/Clad Offset, maximum

Fiber Curl, minimum 4 m | 13.123 ft

Mechanical Specifications

 Macrobending, 20 mm Ø mandrel, 1 turn
 0.75 dB @ 1,550 nm
 1 1.50 dB @ 1,625 nm

 Macrobending, 30 mm Ø mandrel, 10 turns
 0.25 dB @ 1,550 nm
 1 1.00 dB @ 1,625 nm

 Macrobending, 60 mm Ø mandrel, 100 turns
 0.05 dB @ 1,550 nm
 0.05 dB @ 1,625 nm

Dynamic Fatigue Parameter, minimum 20

COMMSCOPE®

CS-8W-IOLT

Optical Specifications

Cabled Cutoff Wavelength, maximum1260 nmPoint Defects, maximum0.1 dB

Zero Dispersion Slope, maximum 0.092 ps/[km-nm-nm]

Zero Dispersion Wavelength, maximum1324 nmZero Dispersion Wavelength, minimum1300 nm

Optical Specifications, Wavelength Specific

Attenuation, maximum 0.22 dB/km @ 1,550 nm | 0.25 dB/km @ 1,490

nm | 0.25 dB/km @ 1,625 nm | 0.36 dB/km @ 1,310

nm | 0.36 dB/km @ 1,385 nm

Attenuation, typical 0.19 dB/km @ 1,550 nm | 0.33 dB/km @ 1,310 nm

Backscatter Coefficient -79.6 dB @ 1,310 nm | -82.1 dB @ 1,550 nm

Dispersion, maximum 18 ps(nm-km) at 1550 nm | 3.5 ps(nm-km) from 1285

nm to 1330 nm at 1310 nm

Index of Refraction 1.467 @ 1,310 nm | 1.467 @ 1,385 nm | 1.468 @ 1,550

nm

1,385 nm

@ 1385 nm

Polarization Mode Dispersion Link Design Value, maximum 0.04 ps/sgrt(km)

Standards Compliance | ITU-T G.652.D | ITU-T G.657.A1 | TIA-492CAAB (OS2)

Environmental Specifications

Heat Aging, maximum 0.05 dB/km @ 85 °C

 Temperature Dependence, maximum
 0.05 dB/km

 Temperature Humidity Cycling, maximum
 0.05 dB/km

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes



CS-8W-IOLT

Temperature Dependence, maximum

Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

Temperature Humidity Cycling, maximum Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

up to 95% relative humidity

