


35422-48



Heat Treated FSJ2RK-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 3/8 in, black non-halogenated, fire retardant polyolefin jacket

Product Classification

Product Type	Coaxial wireless cable
Product Brand	HELIAX® SureFlex®
Product Series	FSJ2-50

General Specifications

Flexibility	Superflexible
Jacket Color	Black
Performance Note	Attenuation values typical, guaranteed within 5%

Dimensions

Diameter Over Dielectric	7.112 mm 0.28 in
Diameter Over Jacket	10.922 mm 0.43 in
Inner Conductor OD	2.794 mm 0.11 in
Outer Conductor OD	9.652 mm 0.38 in
Nominal Size	3/8 in

Electrical Specifications

Cable Impedance	50 ohm ±1 ohm
Capacitance	80 pF/m 24.384 pF/ft
dc Resistance, Inner Conductor	4.232 ohms/km 1.29 ohms/kft
dc Resistance, Outer Conductor	4.987 ohms/km 1.52 ohms/kft
dc Test Voltage	2300 V
Inductance	0.2 µH/m 0.061 µH/ft
Insulation Resistance	100000 MOhms-km
Jacket Spark Test Voltage (rms)	4000 V

35422-48

Operating Frequency Band	1 – 13400 MHz
Peak Power	13.2 kW
Velocity	83 %

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
680–960 MHz	1.201	20.79
1700–2200 MHz	1.201	20.79
2200–2700 MHz	1.433	14.99

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Average Power (kW)
1.0	0.383	0.117	13.2
1.5	0.469	0.143	13.2
2.0	0.542	0.165	13.2
10.0	1.219	0.372	6.97
20.0	1.732	0.528	4.91
30.0	2.128	0.649	3.99
50.0	2.762	0.842	3.08
85.0	3.626	1.105	2.34
88.0	3.691	1.125	2.3
100.0	3.943	1.202	2.16
108.0	4.103	1.25	2.07
150.0	4.864	1.482	1.75
174.0	5.254	1.601	1.62
200.0	5.65	1.722	1.5
204.0	5.709	1.74	1.49
300.0	6.99	2.13	1.22
400.0	8.139	2.481	1.04
450.0	8.665	2.641	0.98
460.0	8.767	2.672	0.97
500.0	9.166	2.794	0.93
512.0	9.283	2.829	0.92
600.0	10.107	3.081	0.84
700.0	10.983	3.347	0.77

35422-48

800.0	11.807	3.599	0.72
824.0	11.998	3.657	0.71
894.0	12.542	3.823	0.68
960.0	13.04	3.974	0.65
1000.0	13.334	4.064	0.64
1218.0	14.861	4.529	0.57
1250.0	15.075	4.595	0.56
1500.0	16.68	5.084	0.51
1700.0	17.887	5.452	0.48
1794.0	18.436	5.619	0.46
1800.0	18.47	5.629	0.46
2000.0	19.599	5.974	0.43
2100.0	20.147	6.141	0.42
2200.0	20.685	6.305	0.41
2300.0	21.214	6.466	0.4
2500.0	22.247	6.781	0.38
2700.0	23.249	7.086	0.37
3000.0	24.701	7.529	0.34
3400.0	26.558	8.094	0.32
3600.0	27.456	8.368	0.31
3700.0	27.899	8.503	0.3
3800.0	28.337	8.637	0.3
3900.0	28.771	8.769	0.3
4000.0	29.201	8.9	0.29
4100.0	29.628	9.03	0.29
4200.0	30.051	9.159	0.28
4300.0	30.47	9.287	0.28
4400.0	30.886	9.414	0.28
4500.0	31.298	9.539	0.27
4600.0	31.708	9.664	0.27
4700.0	32.114	9.788	0.26
4800.0	32.518	9.911	0.26
4900.0	32.919	10.033	0.26
5000.0	33.316	10.154	0.26
6000.0	37.158	11.325	0.23

35422-48

8000.0	44.264	13.491	0.19
8800.0	46.943	14.308	0.18
10000.0	50.826	15.491	0.17
12000.0	57.001	17.373	0.15

Material Specifications

Dielectric Material	Foam PE
Jacket Material	Non-halogenated, fire retardant polyolefin
Inner Conductor Material	Copper-clad aluminum wire
Outer Conductor Material	Corrugated copper

Mechanical Specifications

Minimum Bend Radius, multiple Bends	25.4 mm 1 in
Minimum Bend Radius, single Bend	25.4 mm 1 in
Number of Bends, minimum	30
Number of Bends, typical	50
Tensile Strength	95 kg 209.439 lb
Bending Moment	2.3 N-m 20.357 in lb
Flat Plate Crush Strength	1.8 kg/mm 100.795 lb/in

Environmental Specifications

Installation temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Operating Temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Storage Temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Attenuation, Ambient Temperature	68 °F 20 °C
Average Power, Ambient Temperature	104 °F 40 °C
Average Power, Inner Conductor Temperature	212 °F 100 °C
Fire Retardancy Test Method	NFPA 130-2010 UL 1666/CATVR
Smoke Index Test Method	IEC 61034
Toxicity Index Test Method	IEC 60754-1 IEC 60754-2

Packaging and Weights

Cable weight	0.13 kg/m 0.087 lb/ft
---------------------	-------------------------

Regulatory Compliance/Certifications

Agency

ISO 9001:2015



Classification

Designed, manufactured and/or distributed under this quality management system