

Fiber indoor/outdoor cable, TeraSPEED®, Single Jacket All-Dielectric, Plenum Rated, Multimode/Singlemode, 48 fiber, Gel-Free, Stranded Loose Tube, PVDF jacket, Black jacket color, Feet cable marking

Product Classification

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber indoor/outdoor cable

Product Series P-LN

General Specifications

 Cable Type
 Stranded loose tube

Construction Type Non-armored

Subunit Type Gel-free

Filler, quantity

Jacket Color Black

Jacket Marking Feet

Subunit, quantity 4

Fibers per Subunit, quantity 12

Composite Fiber Count 12 + 36

Total Fiber Count 48


Dimensions


Buffer Tube/Subunit Diameter 2.5 mm | 0.098 in

Diameter Over Jacket 9.7 mm | 0.382 in

Representative Image







Mechanical Specifications

Minimum Bend Radius, loaded

Minimum Bend Radius, unloaded

Tensile Load, long term, maximum

Tensile Load, short term, maximum

Compression

Compression Test Method

Flex

Flex Test Method

Impact

Impact Test Method

Strain

Strain Test Method

Twist

146 mm | 5.748 in

97 mm | 3.819 in

800 N | 179.847 lbf

2700 N | 606.984 lbf

22 N/mm | 125.623 lb/in

FOTP-41 | IEC 60794-1 E3

25 cycles

FOTP-104 | IEC 60794-1 E6

2.94 N-m | 26.021 in lb

FOTP-25 | IEC 60794-1 E4

See long and short term tensile loads

FOTP-33 | IEC 60794-1 E1

10 cycles



Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 880 m | 2,887.139 ft

Optical Specifications

Fiber Type Composite MM/SM | G.652.D and G.657.A1, TeraSPEED® | OM3,

LazrSPEED® 300 | OS2 | OS2

Environmental Specifications

Installation temperature $-30 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-22 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+75 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+167 \,^{\circ}\text{F}$)

Cable Qualification Standards ANSI/ICEA S-104-696 | EN 187105 | Telcordia GR-409

Environmental Space Plenum

Flame Test Listing

NEC OFNP (ETL) and c(ETL)

Flame Test Method

NFPA 130 | NFPA 262

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method FOTP-82 | IEC 60794-1 F5

Environmental Test Specifications

Cable Freeze -2 °C | 28.4 °F

Cable Freeze Test Method FOTP-98 | IEC 60794-1 F15

Heat Age $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-30 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-22 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 92 kg/km | 61.821 lb/kft

Regulatory Compliance/Certifications

Agency Classification



ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

Included Products

CS-5L-LT – LazrSPEED® 300 OM3 Bend-Insensitive Multimode

Fiber

CS-8W-LT - TeraSPEED® G652D/G657A1 Singlemode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

