

Coaxial Drop Cable, 75 Ohm, Series 6, beige PVC jacket



Product Classification

Product Type	Coaxial drop cable
Product Series	6 Series
Warranty	One year

General Specifications

Cable Type	Series 6
Center Conductor Type	Solid
Jacket Color	Black
Jacket Marking	Meters
Performance Note	Attenuation listed represents maximum values at standard condition of 20 °C (68 °F)
Shield Construction Type	Quad shield

Dimensions

Diameter Over Center Conductor, nominal	1.016 mm 0.04 in
Diameter Over Dielectric, nominal	4.572 mm 0.18 in
Diameter Over Inner Shield (Tape), nominal	4.75 mm 0.187 in
Diameter Over Jacket, nominal	7.544 mm 0.297 in
Jacket Thickness, nominal	0.762 mm 0.03 in
Center Conductor Gauge	18 AWG
Inner Shield (Braid) Gauge	34 AWG
Outer Shield (Braid) Gauge	34 AWG

Electrical Specifications

Capacitance	53.15 pF/m 16.2 pF/ft
--------------------	-------------------------

Characteristic Impedance	75 ohm
Characteristic Impedance Tolerance	±3 ohm
dc Resistance Note	Nominal values based on a standard condition of 20 °C (68 °F)
dc Resistance, Inner Conductor, nominal	104.003 ohms/km 31.7 ohms/kft
dc Resistance, Loop, nominal	121.063 ohms/km 36.9 ohms/kft
dc Resistance, Outer Conductor, nominal	17.06 ohms/km 5.2 ohms/kft
Nominal Velocity of Propagation (NVP)	85 %
Operating Frequency Band	5–3000 MHz

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
55.0	5.25	1.6
83.0	6.4	1.95
85.0	6.46	1.97
187.0	9.35	2.85
204.0	9.84	3
211.0	10	3.05
250.0	10.82	3.3
300.0	11.64	3.55
350.0	12.63	3.85
400.0	13.61	4.15
450.0	14.43	4.4
500.0	15.29	4.66
550.0	16.08	4.9
600.0	16.73	5.1
750.0	18.54	5.65
865.0	20.01	6.1
1000.0	21.49	6.55
1200.0	23.68	7.22
1218.0	23.66	7.21
1300.0	24.71	7.53
1400.0	25.71	7.84
1500.0	26.68	8.13
1600.0	27.63	8.42
1700.0	28.54	8.7

1794.0	29.39	8.96
1800.0	29.44	8.97
1900.0	31.31	9.24
2000.0	31.17	9.5
2200.0	32.83	10.01
2500.0	35.2	10.73
3000.0	38.91	11.86

Material Specifications

Center Conductor Material	Copper-clad steel
Dielectric Material	Foam PE
Jacket Material	PVC
Inner Shield (Braid) Coverage	60 %
Inner Shield (Braid) Material	Aluminum
Inner Shield (Tape) Material	Aluminum/Polymer/Aluminum (APA) bonded
Outer Shield (Braid) Coverage	40 %
Outer Shield (Braid) Material	Aluminum
Outer Shield (Tape) Material	Aluminum/Polymer/Aluminum (APA)

Environmental Specifications

Environmental Space	Outdoor
----------------------------	---------

Packaging and Weights

Packaging Type	Reel
Weight, gross	58.038 kg/km 39 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

