
760104729 | 1291B SLT C6A 4/23 F/UTP R3000



GigaSPEED X10D® 1291B ETL Verified Category 6A F/UTP Cable, non-plenum, slate jacket, 4 pair count, 3000 ft (914 m) length, reel

Product Classification

Regional Availability

Asia | Australia/New Zealand | Latin America | North America

Portfolio SYSTIMAX®

Product Type Twisted pair cable
Product Brand GigaSPEED X10D®

General Specifications

Product Number 1291B
ANSI/TIA Category 6A

Cable Component Type Horizontal

Cable Type F/UTP (shielded)

Conductor Type, singlesSolidConductors, quantity8Drain Wire TypeSolidJacket ColorSlate

Pairs, quantity 4

Separator Type Isolator

Transmission Standards ANSI/TIA-568.2-D

Dimensions

Cable Length 914.4 m | 3000 ft

Cable Length Tolerance ±5%

Diameter Over Jacket, nominal7.518 mm | 0.296 inJacket Thickness0.508 mm | 0.02 in


Conductor Gauge, singles 23 AWG

Drain Wire Gauge 26 AWG



760104729 | 1291B SLT C6A 4/23 F/UTP R3000

Cross Section Drawing



Electrical Specifications

dc Resistance Unbalance, maximum 4 %

dc Resistance, maximum 8 ohms/100 m | 2.438 ohms/100 ft

Dielectric Strength, minimum 1500 Vac | 2500 Vdc

LP (Limited Power) Rating 0.5 A

Mutual Capacitance at Frequency 5.6 nF/100 m @ 1 kHz

Nominal Velocity of Propagation (NVP) 68% Operating Frequency, maximum $500\,\mathrm{MHz}$ Operating Voltage, maximum $80\,\mathrm{V}$

Remote Powering Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the

safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2,

CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A

Material Specifications

Conductor MaterialBare copperDrain Wire MaterialTinned copperInsulation MaterialPolyolefinJacket MaterialPVC

Separator Material Polyolefin

Shield (Tape) Material Polyester/Aluminum shield

Page 2 of 3

760104729 | 1291B SLT C6A 4/23 F/UTP R3000

Mechanical Specifications

Pulling Tension, maximum 11.34 kg | 25 lb

Environmental Specifications

Installation temperature $0 \,^{\circ}\text{C}$ to +60 $^{\circ}\text{C}$ (+32 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Operating Temperature $-20 \,^{\circ}\text{C}$ to +60 $^{\circ}\text{C}$ (-4 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Environmental Space Non-plenum

Flame Test Method CMR

Packaging and Weights

Cable weight 52.086 kg/km | 35 lb/kft

Packaging Type Reel

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

