### 760105767 | 1091B LBL C6A 4/23 U/UTP R1000



GigaSPEED X10D® 1091B ETL Verified Category 6A U/UTP Cable, light blue jacket, 4 pair count, 1000 ft (305 m) length, reel

#### Product Classification

Regional Availability

Asia | Australia/New Zealand | Latin America | North America

Portfolio SYSTIMAX®

Product Type Twisted pair cable
Product Brand GigaSPEED X10D®

General Specifications

Product Number 1091B
ANSI/TIA Category 6A

Cable Component Type Horizontal

Cable Type U/UTP (unshielded)

Conductor Type, singles Solid
Conductors, quantity 8

Jacket Color Light blue

Pairs, quantity 4

Separator Type Isolator

**Transmission Standards** ANSI/TIA-568.2-D | ISO/IEC 11801 Class EA

**Dimensions** 

**Cable Length** 304.8 m | 1000 ft


Diameter Over Insulated Conductor0.864 mm | 0.034 inDiameter Over Jacket, nominal7.239 mm | 0.285 inJacket Thickness1.295 mm | 0.051 in

Conductor Gauge, singles 23 AWG

Cross Section Drawing



# 760105767 | 1091B LBL C6A 4/23 U/UTP R1000



### **Electrical Specifications**

Characteristic Impedance100 ohmCharacteristic Impedance Tolerance±15 ohm

dc Resistance Unbalance, maximum  $4\,\%$ 

dc Resistance, maximum 7.61 ohms/100 m | 2.32 ohms/100 ft

**Dielectric Strength, minimum** 1500 Vac | 2500 Vdc

LP (Limited Power) Rating 0.5 A

Mutual Capacitance at Frequency 6.0 nF/100 m @ 1 kHz

Nominal Velocity of Propagation (NVP) 65 %

Operating Frequency, maximum550 MHzOperating Voltage, maximum80 V

**Remote Powering** Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the

safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2,

CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A

Material Specifications

Conductor MaterialBare copperInsulation MaterialPolyolefinJacket MaterialPVC

Page 2 of 3



## 760105767 | 1091B LBL C6A 4/23 U/UTP R1000

Separator MaterialPolyolefinSeparator 2 MaterialPolyolefin

Mechanical Specifications

**Pulling Tension, maximum** 11.34 kg | 25 lb

### **Environmental Specifications**

Installation temperature  $0 \, ^{\circ}\text{C} \text{ to } +60 \, ^{\circ}\text{C} \text{ (+32 } ^{\circ}\text{F to } +140 \, ^{\circ}\text{F)}$ Operating Temperature  $-20 \, ^{\circ}\text{C} \text{ to } +60 \, ^{\circ}\text{C} \text{ (-4 } ^{\circ}\text{F to } +140 \, ^{\circ}\text{F)}$ 

**Environmental Space**Non-plenum **Temperature Rating, UL**90 °C | 194 °F

Flame Test Method CMR

Packaging and Weights

**Cable weight** 55.509 kg/km | 37.3 lb/kft

Packaging Type Reel

#### Regulatory Compliance/Certifications

Ag	ency	Classification
СН	IINA-ROHS	Below maximum concentration value
ISC	9001:2015	Designed, manufactured and/or distributed under this quality management system
RE.	ACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
RO	HS	Compliant
UK	-ROHS	Compliant

