

Fiber OSP cable, TeraSPEED® Single Jacket/Single Armor, 96 fiber, Gel-Free, Stranded Loose Tube, Singlemode G.652.D and G.657.Al, Meters jacket marking, Black jacket color

 Corrugated steel tape armor is strong yet flexible, providing additional crush and rodent protection

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

 Portfolio
 CommScope®

 Product Type
 Fiber OSP cable

Product Series D-LA

General Specifications

Armor Type Corrugated steel

Cable Type Stranded loose tube

Construction Type Armored

Subunit Type Gel-free

Jacket Color Black

Jacket Marking Meters

Subunit, quantity 8

Fibers per Subunit, quantity 12

Total Fiber Count 96


Dimensions

Buffer Tube/Subunit Diameter 2.5 mm | 0.098 in

Diameter Over Jacket 13.4 mm | 0.528 in

Representative Image





Material Specifications

Jacket Material PE

Mechanical Specifications

Minimum Bend Radius, loaded201 mm7.913 inMinimum Bend Radius, unloaded134 mm5.276 inTensile Load, long term, maximum800 N179.847 lbfTensile Load, short term, maximum2700 N606.984 lbf

 Compression
 44 N/mm | 251.246 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 4.41 N-m | 39.032 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 539 m | 1,768.373 ft

Optical Specifications

Fiber Type G.652.D and G.657.A1, TeraSPEED® | OS2



Environmental Specifications

Installation temperature $-30 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C (-22 °F to} + 158 °F)$ Operating Temperature $-40 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C (-40 °F to} + 158 °F)$

Storage Temperature $-40 \,^{\circ}\text{C to} + 75 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to} + 167 \,^{\circ}\text{F})$

Cable Qualification Standards ANSI/ICEA S-87-640 | EN 187105 | Telcordia GR-20

Environmental Space Aerial, lashed | Buried

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Qualification Method ANSI/ICEA S-87-640

Water Penetration Test Method FOTP-82 | IEC 60794-1 F5

Environmental Test Specifications

Cable Freeze -2 °C | 28.4 °F

Cable Freeze Test Method FOTP-98 | IEC 60794-1 F15

Heat Age $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-30 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-22 $^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle -40 °C to +70 °C (-40 °F to +158 °F)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 152 kg/km | 102.139 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant





Included Products

CS-8W-LT

 TeraSPEED® G652D/G657A1 Singlemode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

