

Fiber OSP cable, TeraSPEED® Single Jacket/Single Armor, Gel-Free, 36 fibers, Stranded Loose Tube, Singlemode G.652.D and G.657.A1, Meters jacket marking, Black jacket color

 Corrugated steel tape armor is strong yet flexible, providing additional crush and rodent protection

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

 Portfolio
 CommScope®

 Product Type
 Fiber OSP cable

Product Series D-LA

General Specifications

Armor Type Corrugated steel

Cable Type Stranded loose tube

 Construction Type
 Armored

 Subunit Type
 Gel-free

Filler, quantity 2

Jacket ColorBlackJacket MarkingMeters

Subunit, quantity 3
Fibers per Subunit, quantity 12


**Total Fiber Count** 36

Dimensions

Buffer Tube/Subunit Diameter2.5 mm | 0.098 inDiameter Over Jacket11.5 mm | 0.453 in

## Representative Image





### Material Specifications

Jacket Material PE

### Mechanical Specifications

Minimum Bend Radius, loaded173 mm | 6.811 inMinimum Bend Radius, unloaded115 mm | 4.528 inTensile Load, long term, maximum800 N | 179.847 lbfTensile Load, short term, maximum2700 N | 606.984 lbfCompression22 N/mm | 125.623 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 4.41 N-m | 39.032 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 740 m | 2,427.822 ft

Optical Specifications

**Fiber Type** G.652.D and G.657.A1, TeraSPEED® | OS2



### **Environmental Specifications**

Installation temperature -30 °C to +70 °C (-22 °F to +158 °F) -40 °C to +70 °C (-40 °F to +158 °F) **Operating Temperature Storage Temperature** -40 °C to +75 °C (-40 °F to +167 °F)

**Cable Qualification Standards** ANSI/ICEA S-87-640 | EN 187105 | Telcordia GR-20

**Environmental Space** Aerial, lashed | Buried

UV stabilized **Jacket UV Resistance** 

**Water Penetration** 24 h

**Water Penetration Qualification Method** ANSI/ICEA S-87-640

**Water Penetration Test Method** FOTP-82 | IEC 60794-1 F5

**Environmental Test Specifications** 

**Cable Freeze** -2 °C | 28.4 °F

Cable Freeze Test Method FOTP-98 | IEC 60794-1 F15

**Heat Age** -40 °C to +85 °C (-40 °F to +185 °F)

**Heat Age Test Method** IEC 60794-1 F9

Low High Bend -30 °C to +60 °C (-22 °F to +140 °F)

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

-40 °C to +70 °C (-40 °F to +158 °F) **Temperature Cycle** 

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 110 kg/km | 73.917 lb/kft

### Regulatory Compliance/Certifications

#### CHINA-ROHS Below maximum concentration value

Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

**ROHS** Compliant **UK-ROHS** Compliant



Agency



#### Included Products

CS-8W-LT

 TeraSPEED® G652D/G657A1 Singlemode Fiber

#### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

