

Fiber OSP cable, TeraSPEED® Single Jacket All-Dielectric, Gel-Filled, Central Tube, 24 fibers, Composite OM4 and G.652.D and G.657.Al, Feet jacket marking, Black jacket color

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

 Portfolio
 CommScope®

 Product Type
 Fiber OSP cable

Product Series O-CN

General Specifications

Cable Type Central loose tube

Construction Type Non-armored

Subunit Type Gel-filled

Jacket Color Black

Jacket Marking Feet

Subunit, quantity 2

Fibers per Subunit, quantity 12

Composite Fiber Count 12 + 12

Total Fiber Count 24


Dimensions

Buffer Tube/Subunit Diameter 4 mm | 0.157 in

Diameter Over Jacket 10.28 mm | 0.405 in

Representative Image





Material Specifications

Jacket Material PE

Mechanical Specifications

Minimum Bend Radius, loaded154 mm | 6.063 inMinimum Bend Radius, unloaded103 mm | 4.055 inTensile Load, long term, maximum800 N | 179.847 lbfTensile Load, short term, maximum2700 N | 606.984 lbfCompression22 N/mm | 125.623 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

FIex Test Method FOTP-104 | IEC 60794-1 E6

 Impact
 2.94 N-m | 26.021 in lb

 Impact Test Method
 FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 854 m | 2,801.837 ft

Optical Specifications

Fiber Type Composite MM/SM | G.652.D and G.657.A1, TeraSPEED® | OM4,

LazrSPEED® 550 | OS2

COMMSCOPE®

Environmental Specifications

Installation temperature

-30 °C to +70 °C (-22 °F to +158 °F)

Operating Temperature

-40 °C to +70 °C (-40 °F to +158 °F)

Storage Temperature

-40 °C to +75 °C (-40 °F to +167 °F)

Cable Qualification Standards

ANSI/ICEA S-87-640 | EN 187105

Environmental Space Aerial, lashed | Buried

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method FOTP-82 | IEC 60794-1 F5

Environmental Test Specifications

Cable Freeze -2 °C | 28.4 °F

Cable Freeze Test Method FOTP-98 | IEC 60794-1 F15

Drip 70 °C | 158 °F

Drip Test Method FOTP-81 | IEC 60794-1 E14

Heat Age $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-30 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-22 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 96 kg/km | 64.509 lb/kft

Regulatory Compliance/Certifications

Agency Classification CHINA-ROHS Below maximum concentration value

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system
REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant





Included Products

CS-5K-LT – LazrSPEED® 550 OM4 Bend-Insensitive Multimode

Fiber

CS-8W-LT - TeraSPEED® G652D/G657A1 Singlemode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

