760139873 | 3291B WHT C6A 4/23 F/UTP R3000



GigaSPEED X10D® 3291B Category 6A F/UTP Cable, low smoke zero halogen, white jacket, 4 pair count, 3000 ft (914 m) length, reel

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America

Portfolio SYSTIMAX®

 Product Type
 Twisted pair cable

 Product Brand
 GigaSPEED X10D®

General Specifications

Product Number 3291B
ANSI/TIA Category 6A

Cable Component Type Horizontal

Cable Type F/UTP (shielded)

Conductor Type, singlesSolidConductors, quantity8Drain Wire TypeSolidJacket ColorWhite

Pairs, quantity 4

Separator Type Isolator

Transmission Standards ANSI/TIA-568.2-D

Dimensions

Cable Length 914.4 m | 3000 ft

Cable Length Tolerance ±5%

Diameter Over Jacket, nominal7.518 mm | 0.296 inJacket Thickness0.508 mm | 0.02 in


Conductor Gauge, singles 23 AWG

Drain Wire Gauge 26 AWG



760139873 | 3291B WHT C6A 4/23 F/UTP R3000

Cross Section Drawing



Electrical Specifications

dc Resistance Unbalance, maximum 4 %

dc Resistance, maximum 8 ohms/100 m | 2.438 ohms/100 ft

Mutual Capacitance at Frequency 5.6 nF/100 m @ 1 kHz

Nominal Velocity of Propagation (NVP) 69 %

Operating Frequency, maximum 500 MHz

Operating Voltage, maximum 80 V

Remote Powering Fully complies with the recommendations set forth by IEEE 802.3bt (Type

4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA

TSB-184-A

Segregation Class d

Material Specifications

 Conductor Material
 Bare copper

 Drain Wire Material
 Tinned copper

Insulation Material Polyolefin

Jacket Material Low Smoke Zero Halogen (LSZH)

Separator Material Polyolefin

Shield (Tape) Material Polyester/Aluminum shield

COMMSCOPE®

760139873 | 3291B WHT C6A 4/23 F/UTP R3000

Mechanical Specifications

Pulling Tension, maximum 11.34 kg | 25 lb

Environmental Specifications

Installation temperature 0 °C to +60 °C (+32 °F to +140 °F)

Operating Temperature $-20 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-4 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

Acid Gas Test Method IEC 60754-2

EN50575 CPR Cable EuroClass Fire PerformanceDcaEN50575 CPR Cable EuroClass Smoke Ratings2EN50575 CPR Cable EuroClass Droplets Ratingd2EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Low Smoke Zero Halogen (LSZH)

Flame Test Method IEC 60332-3-22

Smoke Test Method IEC 61034-2

Packaging and Weights

Cable weight 52.309 kg/km | 35.15 lb/kft

Packaging Type Reel

Regulatory Compliance/Certifications

Agency	Classification
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant
CENELEC	

