

Fiber OSP cable, TeraSPEED® Single Jacket All-Dielectric, Gel-Free, Stranded Loose Tube, 24 fibers, Composite OM3 and G.652.D and G.657. Al, Feet jacket marking, Black jacket color


Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber OSP cable
Product Series	D-LN
General Specifications	
Cable Type	Stranded loose tube
Construction Type	Non-armored
Subunit Type	Gel-free
Filler, quantity	3
Jacket Color	Black
Jacket Marking	Feet
Subunit, quantity	2
Fibers per Subunit, quantity	12
Composite Fiber Count	12 + 12
Total Fiber Count	24
Dimensions	
Buffer Tube/Subunit Diameter	2.5 mm 0.098 in
Diameter Over Jacket	10.2 mm 0.402 in

Representative Image

Page 1 of 4





Material Specifications

Jacket Material	PE	
Mechanical Specifications		
Minimum Bend Radius, loaded	153 mm 6.024 in	
Minimum Bend Radius, unloaded	102 mm 4.016 in	
Tensile Load, long term, maximum	800 N 179.847 lbf	
Tensile Load, short term, maximum	2700 N 606.984 lbf	
Compression	22 N/mm 125.623 lb/in	
Compression Test Method	FOTP-41 IEC 60794-1 E3	
Flex	25 cycles	
Flex Test Method	FOTP-104 IEC 60794-1 E6	
Impact	4.41 N-m 39.032 in lb	
Impact Test Method	FOTP-25 IEC 60794-1 E4	
Strain	See long and short term tensile loads	
Strain Test Method	FOTP-33 IEC 60794-1 E1	
Twist	10 cycles	
Twist Test Method	FOTP-85 IEC 60794-1 E7	
Vertical Rise, maximum	1307 m 4,288.058 ft	
Optical Specifications		

Fiber Type

Composite MM/SM | G.652.D and G.657.A1, TeraSPEED® | OM3, LazrSPEED® 300 | OS2

Page 2 of 4



Environmental Specifications

Installation temperature	-30 °C to +70 °C (-22 °F to +158 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +75 °C (-40 °F to +167 °F)
Cable Qualification Standards	ANSI/ICEA S-87-640 EN 187105 Telcordia GR-20
Environmental Space	Aerial, lashed Buried
Jacket UV Resistance	UV stabilized
Water Penetration	24 h
Water Penetration Test Method	FOTP-82 IEC 60794-1 F5

Environmental Test Specifications

Cable Freeze	-2 °C 28.4 °F
Cable Freeze Test Method	FOTP-98 IEC 60794-1 F15
Heat Age	-40 °C to +85 °C (-40 °F to +185 °F)
Heat Age Test Method	IEC 60794-1 F9
Low High Bend	-30 °C to +60 °C (-22 °F to +140 °F)
Low High Bend Test Method	FOTP-37 IEC 60794-1 E11
Temperature Cycle	-40 °C to +70 °C (-40 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3 IEC 60794-1 F1

Packaging and Weights

Cable weight

63 kg/km | 42.334 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

CS-5L-LT

Page 3 of 4



LazrSPEED® 300 OM3 Bend-Insensitive Multimode Fiber

CS-8W-LT

- TeraSPEED® G652D/G657A1 Singlemode Fiber

* Footnotes

_

Operating Temperature Specification applicable to non-terminated bulk fiber cable

Page 4 of 4

