

Fiber OSP cable, TeraSPEED® Single Jacket All-Dielectric, Gel-Free, Stranded Loose Tube, 24 fibers, Composite OM1 and G.652.D and G.657. A1, Feet jacket marking, Black jacket color

#### **Product Classification**

**Regional Availability** Asia | Australia/New Zealand | EMEA | Latin America | North

America

2

**Portfolio** CommScope® **Product Type** Fiber OSP cable

**Product Series** D-LN

General Specifications

**Cable Type** Stranded loose tube

**Construction Type** Non-armored

**Subunit Type** Gel-free

Filler, quantity

**Jacket Color** Black

**Jacket Marking** Feet

Subunit, quantity 12 Fibers per Subunit, quantity

12 + 12**Composite Fiber Count** 


**Total Fiber Count** 24

Dimensions

**Buffer Tube/Subunit Diameter** 2.5 mm | 0.098 in **Diameter Over Jacket** 10.2 mm | 0.402 in

Representative Image





#### Material Specifications

Jacket Material PE

#### Mechanical Specifications

Minimum Bend Radius, loaded153 mm | 6.024 inMinimum Bend Radius, unloaded102 mm | 4.016 inTensile Load, long term, maximum800 N | 179.847 lbfTensile Load, short term, maximum2700 N | 606.984 lbf

 Compression
 22 N/mm | 125.623 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 4.41 N-m | 39.032 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 1307 m | 4,288.058 ft

Optical Specifications

**Fiber Type** Composite MM/SM | G.652.D and G.657.A1, TeraSPEED® | OM1,

OptiSPEED® | OS2

COMMSC PE°

#### **Environmental Specifications**

Installation temperature  $-30 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-22 °F to +158 °F)

Operating Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-40 °F to +158 °F)

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+75 \,^{\circ}\text{C}$  (-40 °F to +167 °F)

Cable Qualification Standards ANSI/ICEA S-87-640 | EN 187105 | Telcordia GR-20

**Environmental Space** Aerial, lashed | Buried

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method FOTP-82 | IEC 60794-1 F5

**Environmental Test Specifications** 

**Cable Freeze** -2 °C | 28.4 °F

Cable Freeze Test Method FOTP-98 | IEC 60794-1 F15

**Heat Age**  $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$ 

**Heat Age Test Method** IEC 60794-1 F9

**Low High Bend**  $-30 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-22 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$ 

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

Temperature Cycle -40 °C to +70 °C (-40 °F to +158 °F)

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 63 kg/km | 42.334 lb/kft

#### Regulatory Compliance/Certifications

### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



#### Included Products

CS-6F-LT

Page 3 of 4



-- -- --

- OptiSPEED® OM1 Multimode Fiber

CS-8W-LT

- TeraSPEED® G652D/G657A1 Singlemode

#### \* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

