760178129 | 1592A BLK C6A 4/23 F/UTP R1000



1592A Category 6A F/UTP filled cable, outdoor, black jacket, aluminum tape shield, inner jacket, 4 pair count, 1000 ft (305 m) length, reel

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America		
Portfolio	SYSTIMAX®		
Product Type	Twisted pair cable		
General Specifications			
Product Number	1592A		
ANSI/TIA Category	6A		
Cable Component Type	Horizontal		
Cable Type	F/UTP (shielded)		
Conductor Type, singles	Solid		
Conductors, quantity	8		
Jacket Color	Black		
Note	Delay has been derated by 6% due to the water proofing agents The maximum permanent link length is reduced from 295 feet to 277 feet as a result of the delay derating		
Pairs, quantity	4		
Separator Type	Isolator		
Transmission Standards	ANSI/TIA-568.2-D ISO/IEC 11801 Class EA		
Dimensions			
Cable Length	304.8 m 1000 ft		
Diameter Over Inner Jacket	6.502 mm 0.256 in		
Diameter Over Insulated Conductor	1.125 mm 0.044 in		
Diameter Over Jacket, nominal	8.382 mm 0.33 in		
Inner Jacket Thickness	0.457 mm 0.018 in		
Jacket Thickness	0.686 mm 0.027 in		
Conductor Gauge, singles	23 AWG		

Page 1 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 14, 2025



760178129 | 1592A BLK C6A 4/23 F/UTP R1000

Cross Section Drawing

Outer Jacket	
Shield ————	
Inner Jacket	
Pair Insulation	
Separator —	
Conductor	
Flooding Compound	
Drain wire	

Electrical Specifications

dc Resistance Unbalance, maximum	5 %	
dc Resistance, maximum	9.38 ohms/100 m 2.859 ohms/100 ft	
Dielectric Strength, minimum	1500 Vac 2500 Vdc	
Mutual Capacitance at Frequency	6.0 nF/100 m @ 1 kHz	
Nominal Velocity of Propagation (NVP)	62 %	
Operating Frequency, maximum	500 MHz	
Operating Voltage, maximum	80 V	
Remote Powering	Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A	
Safety Voltage Rating	300 V	
Material Specifications		
Conductor Material	Bare copper	
Drain Wire Material	Tinned copper	
Insulation Material	Polyolefin	
Jacket Material	PE	
Separator Material	Polyolefin	

Page 2 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 14, 2025



760178129 | 1592A BLK C6A 4/23 F/UTP R1000

Shield (Tape) Material		Aluminum/Poly	
Mechanical Specifications			
Pulling Tension, maximur	n	11.34 kg 25 lb	
Environmental Specifications			
Installation temperature		-30 °C to +70 °C (-22 °F to +158 °F)	
Operating Temperature		-40 °C to +70 °C (-40 °F to +158 °F)	
Environmental Note		UV resistant for outdoor and/or direct burial installations	
Environmental Space		Buried	
Packaging and Weights			
Cable weight		64.735 kg/km 43.5 lb/kft	
Packaging Type		Reel	
Regulatory Compliance/Certifications			
Agency	Classification		
CHINA-ROHS	Below maximum concentration value		
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system		
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance		
ROHS	Compliant		
UK-ROHS	Compliant		

æ

Page 3 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 14, 2025

