760213595 | D-048-CN-RB-F12NS/5L/99A



Fiber OSP Cable, Non-Armored, All-Dielectric, Arid-Core, 48 fibers, Dry Central Tube Ribbon, Multimode OM3 bend insensitive, Gel-free, Feet jacket marking, Black jacket color

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

Portfolio CommScope®

Product Type Fiber OSP cable

Product Series D-CN

General Specifications

Cable Type Ribbon central tube

Construction Type Non-armored

Subunit Type Gel-free

Fibers per Ribbon, quantity 12

Jacket Color Black

Jacket Marking Feet

Total Fiber Count 48

Dimensions


Buffer Tube/Subunit Diameter 6 mm | 0.236 in

Diameter Over Jacket 12.6 mm | 0.496 in

Representative Image



760213595 | D-048-CN-RB-F12NS/5L/99A



Mechanical Specifications

Minimum Bend Radius, loaded 251.5 mm | 9.902 in

Minimum Bend Radius, unloaded 127 mm | 5 in

Tensile Load, long term, maximum 800 N | 179.847 lbf

Tensile Load, short term, maximum 2700 N | 606.984 lbf

Compression 22 N/mm | 125.623 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 4.4 N-m | 38.943 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Optical Specifications

Fiber Type OM3, bend insensitive | OM3, bend insensitive

Environmental Specifications

Installation temperature $-30 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-22 $^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Page 2 of 3



760213595 | D-048-CN-RB-F12NS/5L/99A

Storage Temperature -40 °C to +75 °C (-40 °F to +167 °F)

Cable Qualification Standards ANSI/ICEA S-87-640 | Telcordia GR-20

Environmental Space Aerial, lashed | Buried

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method FOTP-82 | IEC 60794-1 F5

Environmental Test Specifications

Heat Age $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-30 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-22 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 130 kg/km | 87.356 lb/kft

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Included Products

CS-5Y-RB - 50µm OM3 Bend-Insensitive Multimode

Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

