760213785 | D-036-CA-RB-F12NS/8W/99A



Fiber OSP cable, Steel Armored, Arid-Core, Dry Central Tube Ribbon, 36 fiber, Singlemode G.652.D and G.657.A1, Feet jacket marking, Black jacket color

*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

Feet

Portfolio CommScope®

Product Type Fiber OSP cable

Product Series D-CA

Government RequirementsBuild America Buy America (BABA) compliant*

General Specifications

Armor Type Corrugated steel

Cable Type Ribbon central tube

Construction TypeArmoredSubunit TypeGel-free

Fibers per Ribbon, quantity 12

Jacket Color Black

Location of Manufacturing Carrollton, Georgia

Total Fiber Count 36

Dimensions

Jacket Marking


Buffer Tube/Subunit Diameter 6 mm | 0.236 in

Diameter Over Jacket 13 mm | 0.512 in

Representative Image



760213785 | D-036-CA-RB-F12NS/8W/99A



Mechanical Specifications

Minimum Bend Radius, loaded 259.1 mm | 10.201 in

Minimum Bend Radius, unloaded 129.5 mm | 5.098 in

Tensile Load, long term, maximum800 N | 179.847 lbf **Tensile Load, short term, maximum**2700 N | 606.984 lbf

Tensile Load, short term, maximum 2700 N | 606.984 lbf

Compression 22 N/mm | 125.623 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 4.4 N-m | 38.943 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Optical Specifications

Fiber Type G.652.D and G.657.A1 | G.652.D and G.657.A1

Environmental Specifications



760213785 | D-036-CA-RB-F12NS/8W/99A

Installation temperature $-30 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-22 °F to +140 °F)

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 °F to +158 °F)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+75 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+167 \,^{\circ}\text{F}$)

Cable Qualification Standards ANSI/ICEA S-87-640 | Telcordia GR-20

Environmental SpaceAerial, lashed | Buried

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method FOTP-82 | IEC 60794-1 F5

Environmental Test Specifications

Heat Age -40 °C to +85 °C (-40 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-30 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-22 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle -40 °C to +70 °C (-40 °F to +158 °F)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 163 kg/km | 109.531 lb/kft

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Included Products

CS-8W-RB-OUTDOOR - TeraSPEED® Singlemode Fiber Rollable Ribbon

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

