

Fiber indoor cable, TeraSPEED® Plenum MPO Trunk, 72 fiber multi-unit with 12 fiber subunits, Composite OM4 and G.652.D and G.657.A1, Gel-free, Feet jacket marking, Red jacket color

Product Classification

|                       |                                                                                    |
|-----------------------|------------------------------------------------------------------------------------|
| Regional Availability | Asia   Australia/New Zealand   Latin America   Middle East /Africa   North America |
| Portfolio             | CommScope®                                                                         |
| Product Type          | Fiber indoor cable                                                                 |
| Product Series        | P-MP                                                                               |


General Specifications

|                              |                 |
|------------------------------|-----------------|
| Cable Type                   | MPO trunk cable |
| Construction Type            | Non-armored     |
| Subunit Type                 | Gel-free        |
| Jacket Color                 | Red             |
| Jacket Marking               | Feet            |
| Subunit, quantity            | 6               |
| Fibers per Subunit, quantity | 12              |
| Composite Fiber Count        | 36 + 36         |
| Total Fiber Count            | 72              |

Dimensions

|                              |                    |
|------------------------------|--------------------|
| Buffer Tube/Subunit Diameter | 3 mm   0.118 in    |
| Diameter Over Jacket         | 10.7 mm   0.421 in |

Representative Image



## Mechanical Specifications

|                                   |                                       |
|-----------------------------------|---------------------------------------|
| Minimum Bend Radius, loaded       | 161 mm   6.339 in                     |
| Minimum Bend Radius, unloaded     | 107 mm   4.213 in                     |
| Tensile Load, long term, maximum  | 400 N   89.924 lbf                    |
| Tensile Load, short term, maximum | 1335 N   300.12 lbf                   |
| Compression                       | 10 N/mm   57.101 lb/in                |
| Compression Test Method           | FOTP-41   IEC 60794-1 E3              |
| Flex                              | 300 cycles                            |
| Flex Test Method                  | FOTP-104   IEC 60794-1 E6             |
| Impact                            | 0.74 N-m   6.55 in lb                 |
| Impact Test Method                | FOTP-25   IEC 60794-1 E4              |
| Strain                            | See long and short term tensile loads |
| Strain Test Method                | FOTP-33   IEC 60794-1 E1              |
| Twist                             | 10 cycles                             |
| Twist Test Method                 | FOTP-85   IEC 60794-1 E7              |
| Vertical Rise, maximum            | 368 m   1,207.349 ft                  |

## Optical Specifications

|            |                                                                                      |
|------------|--------------------------------------------------------------------------------------|
| Fiber Type | Composite MM/SM   G.652.D and G.657.A1, TeraSPEED®   OM4, LazrSPEED® 550   OS2   OS2 |
|------------|--------------------------------------------------------------------------------------|

## Environmental Specifications

|                          |                                    |
|--------------------------|------------------------------------|
| Installation temperature | 0 °C to +70 °C (+32 °F to +158 °F) |
| Operating Temperature    | 0 °C to +70 °C (+32 °F to +158 °F) |

|                               |                                       |
|-------------------------------|---------------------------------------|
| Storage Temperature           | -40 °C to +70 °C (-40 °F to +158 °F)  |
| Cable Qualification Standards | ANSI/ICEA S-83-596   Telcordia GR-409 |
| Environmental Space           | Plenum                                |
| Flame Test Listing            | NEC OFNP (ETL) and c(ETL)             |
| Flame Test Method             | NFPA 130   NFPA 262                   |

## Environmental Test Specifications

|                               |                                    |
|-------------------------------|------------------------------------|
| Heat Age                      | 0 °C to +85 °C (+32 °F to +185 °F) |
| Heat Age Test Method          | IEC 60794-1 F9                     |
| Low High Bend                 | 0 °C to +70 °C (+32 °F to +158 °F) |
| Low High Bend Test Method     | FOTP-37   IEC 60794-1 E11          |
| Temperature Cycle             | 0 °C to +70 °C (+32 °F to +158 °F) |
| Temperature Cycle Test Method | FOTP-3   IEC 60794-1 F1            |

## Packaging and Weights

|              |                           |
|--------------|---------------------------|
| Cable weight | 111 kg/km   74.589 lb/kft |
|--------------|---------------------------|

## Regulatory Compliance/Certifications

| Agency        | Classification                                                                 |
|---------------|--------------------------------------------------------------------------------|
| CHINA-ROHS    | Below maximum concentration value                                              |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| ROHS          | Compliant                                                                      |
| UK-ROHS       | Compliant                                                                      |



## Included Products

|          |                                                       |
|----------|-------------------------------------------------------|
| CS-5K-MP | - LazrSPEED® 550 OM4 Bend-Insensitive Multimode Fiber |
| CS-8W-MP | - TeraSPEED® OS2 Singlemode Fiber                     |

## \* Footnotes

|                       |                                                             |
|-----------------------|-------------------------------------------------------------|
| Operating Temperature | Specification applicable to non-terminated bulk fiber cable |
|-----------------------|-------------------------------------------------------------|

## LazrSPEED® 550

### Product Classification

|              |               |
|--------------|---------------|
| Portfolio    | CommScope®    |
| Product Type | Optical fiber |

### General Specifications

|                                               |                        |
|-----------------------------------------------|------------------------|
| Cladding Diameter                             | 125 µm                 |
| Cladding Diameter Tolerance                   | ±5 µm                  |
| Cladding Non-Circularity, maximum             | 1 %                    |
| Coating Diameter (Colored)                    | 254 µm                 |
| Coating Diameter (Uncolored)                  | 245 µm                 |
| Coating Diameter Tolerance (Colored)          | ±7 µm                  |
| Coating Diameter Tolerance (Uncolored)        | ±10 µm                 |
| Coating/Cladding Concentricity Error, maximum | 12 µm                  |
| Core Diameter                                 | 50 µm                  |
| Core Diameter Tolerance                       | ±2.5 µm                |
| Core/Clad Offset, maximum                     | 1.5 µm                 |
| Proof Tensile Stress                          | 100,000 psi (0.69 GPa) |

### Mechanical Specifications

|                                          |                                       |
|------------------------------------------|---------------------------------------|
| Macrobending, 15 mm Ø mandrel, 2 turns   | 0.20 dB @ 850 nm   0.50 dB @ 1,300 nm |
| Macrobending, 30 mm Ø mandrel, 2 turns   | 0.10 dB @ 850 nm   0.30 dB @ 1,300 nm |
| Macrobending, 75 mm Ø mandrel, 100 turns | 0.50 dB @ 1,300 nm   0.50 dB @ 850 nm |
| Coating Strip Force, maximum             | 8.9 N   2.001 lbf                     |
| Coating Strip Force, minimum             | 1.3 N   0.292 lbf                     |
| Dynamic Fatigue Parameter, minimum       | 18                                    |

### Optical Specifications

|                    |     |
|--------------------|-----|
| Numerical Aperture | 0.2 |
|--------------------|-----|

# CS-5K-MP

|                                     |                     |
|-------------------------------------|---------------------|
| Numerical Aperture Tolerance        | ±0.015              |
| Point Defects, maximum              | 0.15 dB             |
| Zero Dispersion Slope, maximum      | 0.105 ps/[km-nm-nm] |
| Zero Dispersion Wavelength, maximum | 1316 nm             |
| Zero Dispersion Wavelength, minimum | 1297 nm             |

## Optical Specifications, Wavelength Specific

|                              |                                                               |
|------------------------------|---------------------------------------------------------------|
| 1 Gbps Ethernet Distance     | 1,110 m @ 850 nm   600 m @ 1,300 nm                           |
| 10 Gbps Ethernet Distance    | 550 m @ 850 nm                                                |
| Attenuation, maximum         | 1.00 dB/km @ 1,300 nm   3.00 dB/km @ 850 nm                   |
| Backscatter Coefficient      | -68.0 dB @ 850 nm   -75.7 dB @ 1,300 nm                       |
| Bandwidth, Laser, minimum    | 4,700 MHz-km @ 850 nm   500 MHz-km @ 1,300 nm                 |
| Bandwidth, OFL, minimum      | 3,500 MHz-km @ 850 nm   500 MHz-km @ 1,300 nm                 |
| Differential Mode Delay      | 0.70 ps/m @ 850 nm                                            |
| Differential Mode Delay Note | Superior to ANSI/TIA TIA-492AAAF and IEC 60793-2-10 at 850 nm |
| Index of Refraction          | 1.479 @ 1,300 nm   1.483 @ 850 nm                             |
| Standards Compliance         | ANSI/TIA-492AAAF (OM4)   IEC 60793-2-10, A1 (OM4)             |

## Environmental Specifications

|                                       |                    |
|---------------------------------------|--------------------|
| Heat Aging, maximum                   | 0.20 dB/km @ 85 °C |
| Temperature Dependence, maximum       | 0.1 dB/km          |
| Temperature Humidity Cycling, maximum | 0.2 dB/km          |
| Water Immersion, maximum              | 0.20 dB/km @ 23 °C |

## Regulatory Compliance/Certifications

| Agency        | Classification                                                                 |
|---------------|--------------------------------------------------------------------------------|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

## \* Footnotes

|                                       |                                                                                                               |
|---------------------------------------|---------------------------------------------------------------------------------------------------------------|
| Temperature Dependence, maximum       | Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)                                   |
| Temperature Humidity Cycling, maximum | Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F) up to 95% relative humidity |

TeraSPEED®

TeraSPEED® OS2 Singlemode Fiber

Product Classification

|              |               |
|--------------|---------------|
| Portfolio    | CommScope®    |
| Product Type | Optical fiber |

General Specifications

|                                               |                        |
|-----------------------------------------------|------------------------|
| Cladding Diameter                             | 125 µm                 |
| Cladding Diameter Tolerance                   | ±0.7 µm                |
| Cladding Non-Circularity, maximum             | 0.7 %                  |
| Coating Diameter (Colored)                    | 249 µm                 |
| Coating Diameter (Uncolored)                  | 242 µm                 |
| Coating Diameter Tolerance (Colored)          | ±13 µm                 |
| Coating Diameter Tolerance (Uncolored)        | ±5 µm                  |
| Coating/Cladding Concentricity Error, maximum | 12 µm                  |
| Core Diameter                                 | 8.3 µm                 |
| Core/Clad Offset, maximum                     | 0.5 µm                 |
| Proof Tensile Stress                          | 100,000 psi (0.69 GPa) |

Dimensions

|                     |                 |
|---------------------|-----------------|
| Fiber Curl, minimum | 4 m   13.123 ft |
|---------------------|-----------------|

Mechanical Specifications

|                                          |                                         |
|------------------------------------------|-----------------------------------------|
| Macrobending, 20 mm Ø mandrel, 1 turn    | 0.75 dB @ 1,550 nm   1.50 dB @ 1,625 nm |
| Macrobending, 30 mm Ø mandrel, 10 turns  | 0.25 dB @ 1,550 nm   1.00 dB @ 1,625 nm |
| Macrobending, 60 mm Ø mandrel, 100 turns | 0.05 dB @ 1,550 nm   0.05 dB @ 1,625 nm |
| Coating Strip Force, maximum             | 8.9 N   2.001 lbf                       |
| Coating Strip Force, minimum             | 1.3 N   0.292 lbf                       |
| Dynamic Fatigue Parameter, minimum       | 20                                      |

# CS-8W-MP

## Optical Specifications

|                                     |                     |
|-------------------------------------|---------------------|
| Cabled Cutoff Wavelength, maximum   | 1260 nm             |
| Point Defects, maximum              | 0.1 dB              |
| Zero Dispersion Slope, maximum      | 0.092 ps/[km-nm-nm] |
| Zero Dispersion Wavelength, maximum | 1324 nm             |
| Zero Dispersion Wavelength, minimum | 1300 nm             |

## Optical Specifications, Wavelength Specific

|                                                         |                                                                                                                                               |
|---------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|
| Attenuation, maximum                                    | 0.40 dB/km @ 1,310 nm   0.40 dB/km @ 1,385 nm   0.40 dB/km @ 1,490 nm   0.40 dB/km @ 1,550 nm   0.50 dB/km @ 1,270 nm   0.50 dB/km @ 1,575 nm |
| Backscatter Coefficient                                 | -79.6 dB @ 1,310 nm   -82.1 dB @ 1,550 nm                                                                                                     |
| Dispersion, maximum                                     | 18 ps(nm-km) at 1550 nm   3.5 ps(nm-km) from 1285 nm to 1330 nm at 1310 nm                                                                    |
| Index of Refraction                                     | 1.467 @ 1,310 nm   1.467 @ 1,385 nm   1.468 @ 1,550 nm                                                                                        |
| Mode Field Diameter                                     | 10.4 μm @ 1,550 nm   9.2 μm @ 1,310 nm   9.6 μm @ 1,385 nm                                                                                    |
| Mode Field Diameter Tolerance                           | ±0.4 μm @ 1310 nm   ±0.5 μm @ 1550 nm   ±0.6 μm @ 1385 nm                                                                                     |
| Polarization Mode Dispersion Link Design Value, maximum | 0.04 ps/sqrt(km)                                                                                                                              |
| Standards Compliance                                    | ITU-T G.652.D   ITU-T G.657.A1   TIA-492CAAB (OS2)                                                                                            |

## Environmental Specifications

|                                       |                    |
|---------------------------------------|--------------------|
| Heat Aging, maximum                   | 0.05 dB/km @ 85 °C |
| Temperature Dependence, maximum       | 0.05 dB/km         |
| Temperature Humidity Cycling, maximum | 0.05 dB/km         |
| Water Immersion, maximum              | 0.05 dB/km @ 23 °C |

## Regulatory Compliance/Certifications

| Agency        | Classification                                                                 |
|---------------|--------------------------------------------------------------------------------|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

## \* Footnotes

|                                 |                                                                             |
|---------------------------------|-----------------------------------------------------------------------------|
| Temperature Dependence, maximum | Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F) |
|---------------------------------|-----------------------------------------------------------------------------|

# CS-8W-MP

---

**Temperature Humidity Cycling, maximum** Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F) up to 95% relative humidity