760213983 | D-216-CA-RB-F12NS/5L/99A



Fiber OSP cable, Steel Armored, Arid-Core, Dry Central Tube Ribbon, 216 fiber, Multimode OM3, bend insensitive, Feet jacket marking, Black jacket color

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

 Portfolio
 CommScope®

 Product Type
 Fiber OSP cable

Product Series D-CA

General Specifications

Armor Type Corrugated steel

 Cable Type
 Ribbon central tube

Construction TypeArmoredSubunit TypeGel-free

Fibers per Ribbon, quantity 12

Jacket Color Black

Jacket Marking Feet
Total Fiber Count 216


Dimensions

Buffer Tube/Subunit Diameter10.4 mm0.409 inDiameter Over Jacket18 mm0.709 in

Representative Image



760213983 | D-216-CA-RB-F12NS/5L/99A



Mechanical Specifications

Minimum Bend Radius, loaded

Minimum Bend Radius, unloaded

Tensile Load, long term, maximum

Tensile Load, short term, maximum

Compression

Compression Test Method

Flex

Flex Test Method

Impact

Impact Test Method

Strain

Strain Test Method

Twist

Twist Test Method

Optical Specifications

Fiber Type

360.7 mm | 14.201 in

180.3 mm | 7.098 in

800 N | 179.847 lbf

2700 N | 606.984 lbf

22 N/mm | 125.623 lb/in

FOTP-41 | IEC 60794-1 E3

25 cycles

FOTP-104 | IEC 60794-1 E6

4.4 N-m | 38.943 in lb

FOTP-25 | IEC 60794-1 E4

See long and short term tensile loads

FOTP-33 | IEC 60794-1 E1

10 cycles

FOTP-85 | IEC 60794-1 E7

OM3, bend insensitive | OM3, bend insensitive

Environmental Specifications



760213983 | D-216-CA-RB-F12NS/5L/99A

Installation temperature $-30 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-22 $^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Storage Temperature -40 °C to +75 °C (-40 °F to +167 °F)

Cable Qualification Standards ANSI/ICEA S-87-640 | Telcordia GR-20

Environmental SpaceAerial, lashed | Buried

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method FOTP-82 | IEC 60794-1 F5

Environmental Test Specifications

Heat Age -40 °C to +85 °C (-40 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-30 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-22 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle -40 °C to +70 °C (-40 °F to +158 °F)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 256 kg/km | 172.024 lb/kft

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Included Products

CS-5Y-RB - 50µm OM3 Bend-Insensitive Multimode

Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

