
# 760219691 | N-096-MP-5K-F12AQ/20T/D



Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 96 fiber multi-unit with 12 fiber 2.0mm subunits, Gel-free, Multimode OM4, Feet jacket marking, Aqua jacket color, Dca flame rating

### Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber indoor cable
Product Series	N-MP
General Specifications	
Cable Type	MPO trunk cable
Construction Type	Non-armored
Subunit Type	Gel-free
Jacket Color	Aqua
Jacket Marking	Feet
Subunit, quantity	8
Fibers per Subunit, quantity	12
Total Fiber Count	96
Dimensions	
Buffer Tube/Subunit Diameter	2 mm   0.079 in
Diameter Over Jacket	9.3 mm   0.366 in

## Representative Image

Page 1 of 7



#### N-096-MP-5K-F12AQ/20T/D 760219691 |



## Mechanical Specifications

Minimum Bend Radius, loaded	139 mm   5.472 in	
Minimum Bend Radius, unloaded	93 mm   3.661 in	
Tensile Load, long term, maximum	200 N   44.962 lbf	
Tensile Load, short term, maximum	667 N   149.948 lbf	
Compression	10 N/mm   57.101 lb/in	
Compression Test Method	FOTP-41   IEC 60794-1 E3	
Flex	25 cycles	
Flex Test Method	FOTP-104   IEC 60794-1 E6	
Impact	2.94 N-m   26.021 in lb	
Impact Test Method	FOTP-25   IEC 60794-1 E4	
Strain	See long and short term tensile loads	
Strain Test Method	FOTP-33   IEC 60794-1 E1	
Twist	10 cycles	
Twist Test Method	FOTP-85   IEC 60794-1 E7	
Vertical Rise, maximum	233 m   764.436 ft	
Optical Specifications		
Fiber Type	OM4, LazrSPEED® 550   OM4, LazrSPEED® 550	

## **Environmental Specifications**

Installation temperature	0 °C to +60 °C (+32 °F to +140 °F)
Operating Temperature	0 °C to +70 °C (+32 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

Page 2 of 7



## 760219691 | N-096-MP-5K-F12AQ/20T/D

Cable Qualification Standards	ANSI/ICEA S-83-596   Telcordia GR-409
EN50575 CPR Cable EuroClass Fire Performance	Dca
EN50575 CPR Cable EuroClass Smoke Rating	s1a
EN50575 CPR Cable EuroClass Droplets Rating	d1
EN50575 CPR Cable EuroClass Acidity Rating	a1
Environmental Space	Low Smoke Zero Halogen (LSZH)   Riser
Flame Test Listing	NEC OFNR-ST1 (ETL) and c(ETL)
Flame Test Method	CSA FT4   IEC 60332-3   IEC 60754-2   IEC 61034-2   UL 1666   UL 1685

## Environmental Test Specifications

Heat Age	0 °C to +85 °C (+32 °F to +185 °F)	
Heat Age Test Method	thod IEC 60794-1 F9	
Low High Bend	0 °C to +60 °C (+32 °F to +140 °F)	
ow High Bend Test Method FOTP-37   IEC 60794-1 E11		
Temperature Cycle 0 °C to +70 °C (+32 °F to +158 °F		
Temperature Cycle Test Method	FOTP-3   IEC 60794-1 F1	

#### Packaging and Weights

Cable weight

76.6 kg/km | 51.473 lb/kft

## Regulatory Compliance/Certifications

Agency	Classification
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

## Included Products

CS-5K-MP

LazrSPEED® 550 OM4 Bend-Insensitive Multimode Fiber

Page 3 of 7



## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

Page 4 of 7



#### LazrSPEED® 550 OM4 Bend-Insensitive Multimode Fiber

## LazrSPEED® 550

## Product Classification

Portfolio	CommScope®
Product Type	Optical fiber
General Specifications	
Cladding Diameter	125 µm
Cladding Diameter Tolerance	±0.8 µm
Cladding Non-Circularity, maximum	1 %
Coating Diameter (Colored)	254 µm
Coating Diameter (Uncolored)	245 µm
Coating Diameter Tolerance (Colored)	±7 μm
Coating Diameter Tolerance (Uncolored)	±10 μm
Coating/Cladding Concentricity Error, maximum	12 µm
Core Diameter	50 µm
Core Diameter Tolerance	±2.5 µm
Core/Clad Offset, maximum	1.5 µm
Proof Test	689.476 N/mm <sup>2</sup>   100000 psi

## Mechanical Specifications

Macrobending, 15 mm Ø mandrel, 2 turns	0.20 dB @ 850 nm   0.50 dB @ 1,300 nm
Macrobending, 30 mm Ø mandrel, 2 turns	0.10 dB @ 850 nm   0.30 dB @ 1,300 nm
Macrobending, 75 mm Ø mandrel, 100 turns	0.50 dB @ 1,300 nm   0.50 dB @ 850 nm
Coating Strip Force, maximum	8.9 N   2.001 lbf
Coating Strip Force, minimum	1.3 N   0.292 lbf
Dynamic Fatigue Parameter, minimum	18

Page 5 of 7



## CS-5K-MP

## **Optical Specifications**

Numerical Aperture	0.2
Numerical Aperture Tolerance	±0.015
Point Defects, maximum	0.15 dB
Zero Dispersion Slope, maximum	0.105 ps/[km-nm-nm]
Zero Dispersion Wavelength, maximum	1316 nm
Zero Dispersion Wavelength, minimum	1297 nm

## Optical Specifications, Wavelength Specific

1 Gbps Ethernet Distance	1,110 m @ 850 nm   600 m @ 1,300 nm	
10 Gbps Ethernet Distance	550 m @ 850 nm	
Attenuation, maximum	1.00 dB/km @ 1,300 nm   3.00 dB/km @ 850 nm	
Backscatter Coefficient	-68.0 dB @ 850 nm   -75.7 dB @ 1,300 nm	
Bandwidth, Laser, minimum	4,700 MHz-km @ 850 nm   500 MHz-km @ 1,300 nm	
Bandwidth, OFL, minimum	3,500 MHz-km @ 850 nm 🕴 500 MHz-km @ 1,300 nm	
Differential Mode Delay	0.70 ps/m @ 850 nm	
Differential Mode Delay Note	Superior to ANSI/TIA TIA-492AAAF and IEC 60793-2-10 at 850 nm	
Index of Refraction	1.479 @ 1,300 nm   1.483 @ 850 nm	
Standards Compliance	ANSI/TIA-492AAAF (OM4)   IEC 60793-2-10, A1 (OM4)	

## **Environmental Specifications**

Heat Aging, maximum	0.20 dB/km @ 85 °C
Temperature Dependence, maximum	0.1 dB/km
Temperature Humidity Cycling, maximum	0.2 dB/km
Water Immersion, maximum	0.20 dB/km @ 23 °C

#### Regulatory Compliance/Certifications

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

## \* Footnotes

Temperature Dependence, maximum	Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)
Temperature Humidity Cycling, maximum	Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

Page 6 of 7





up to 95% relative humidity

Page 7 of 7

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 20, 2024

COMMSCOPE®