
760216549 | P-024-MP-5G-F12LM



Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, 24 fiber with 12 fiber subunits, Multimode OM5, Feet jacket marking, Lime green jacket color

Product Classification

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber indoor cable

Product Series P-MP

General Specifications

Cable Type MPO trunk cable

Construction Type Non-armored

Subunit Type Gel-free

Jacket Color Lime green

Jacket Marking Feet

Subunit, quantity 2

Fibers per Subunit, quantity 12

Total Fiber Count 24


Dimensions

Height Over Jacket3.9 mm0.154 inWidth Over Jacket6.9 mm0.272 inBuffer Tube/Subunit Diameter3 mm0.118 in

Representative Image



760216549 | P-024-MP-5G-F12LM



Mechanical Specifications

Minimum Bend Radius, loaded 58 mm | 2.283 in

Minimum Bend Radius, unloaded39 mm | 1.535 inTensile Load, long term, maximum200 N | 44.962 lbf

Tensile Load, short term, maximum 667 N | 149.948 lbf

Compression 10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 0.74 N-m | 6.55 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 500 m | 1,640.42 ft

Optical Specifications

Fiber Type OM5, LazrSPEED® wideband | OM5, LazrSPEED® wideband

Environmental Specifications

Installation temperature $0 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C (+32 °F to} + 158 \,^{\circ}\text{F)}$ Operating Temperature $0 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C (+32 °F to} + 158 \,^{\circ}\text{F)}$

Page 2 of 5



760216549 | P-024-MP-5G-F12LM

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

Environmental Space Plenum

Flame Test Listing

NEC OFNP (ETL) and c(ETL)

Flame Test Method

NFPA 130 | NFPA 262

Environmental Test Specifications

Heat Age 0 °C to +85 °C (+32 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

Low High Bend $0 \degree \text{C to } +70 \degree \text{C (} +32 \degree \text{F to } +158 \degree \text{F)}$

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle 0 °C to +70 °C (+32 °F to +158 °F)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 29 kg/km | 19.487 lb/kft

Regulatory Compliance/Certifications

on
C

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

CS-5G-MP - LazrSPEED® OM5 WideBand Multimode

Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable



LazrSPEED®

LazrSPEED® OM5 WideBand Multimode Fiber

Product Classification

 Portfolio
 CommScope®

 Product Type
 Optical fiber

General Specifications

Cladding Diameter 125 µm **Cladding Diameter Tolerance** ±5 µm Cladding Non-Circularity, maximum 0.7 % **Coating Diameter (Colored)** 254 µm **Coating Diameter (Uncolored)** 242 µm **Coating Diameter Tolerance (Colored)** ±7 µm **Coating Diameter Tolerance (Uncolored)** ±5 µm Coating/Cladding Concentricity Error, maximum 12 µm **Core Diameter** 50 µm **Core Diameter Tolerance** ±2.5 µm

Proof Tensile Stress 100,000 psi (0.69 GPa)

Mechanical Specifications

Core/Clad Offset, maximum

 Macrobending, 15 mm Ø mandrel, 2 turns
 0.20 dB @ 850 nm | 0.50 dB @ 1,300 nm

 Macrobending, 30 mm Ø mandrel, 2 turns
 0.10 dB @ 850 nm | 0.30 dB @ 1,300 nm

 Macrobending, 75 mm Ø mandrel, 100 turns
 0.50 dB @ 1,300 nm | 0.50 dB @ 850 nm

1 µm

Coating Strip Force, maximum $4.5 \, \text{N}$ | $1.012 \, \text{lbf}$ Coating Strip Force, minimum $0.9 \, \text{N}$ | $0.202 \, \text{lbf}$

Dynamic Fatigue Parameter, minimum 18

Optical Specifications

Numerical Aperture 0.2

COMMSCOPE®

CS-5G-MP

Numerical Aperture Tolerance ±0.010

Point Defects, maximum 0.15 dB

Zero Dispersion Slope, maximum (OM5) $-412/(840(1-(\lambda 0/840)^4)))$ ps/[km-nm-nm]

Zero Dispersion Wavelength, maximum1328 nmZero Dispersion Wavelength, minimum1297 nm

Optical Specifications, Wavelength Specific

1 Gbps Ethernet Distance 1,110 m @ 850 nm | 600 m @ 1,300 nm

10 Gbps Ethernet Distance 550 m @ 850 nm

Attenuation, maximum 1.00 dB/km @ 1,300 nm | 2.20 dB/km @ 953 nm | 3.00 dB/km @

850 nm

Bandwidth, Laser, minimum 2,600 MHz-km @ 953 nm | 4,700 MHz-km @ 850 nm | 500 MHz-km

@ 1,300 nm

Bandwidth, OFL, minimum 1,950 MHz-km @ 953 nm | 3,500 MHz-km @ 850 nm | 500 MHz-km

@ 1,300 nm

Index of Refraction 1.478 @ 1,300 nm | 1.483 @ 850 nm

Standards Compliance ANSI/TIA-492AAAF (OM5) | ANSI/TIA-568.3 (OM5) | IEC 60793-2-10,

A1 (OM5) | ISO/IEC 11801-1 cabled optical fiber performance category

OM5

Environmental Specifications

Heat Aging, maximum 0.10 dB/km @ 85 °C

Temperature Dependence, maximum 0.1 dB/km
Temperature Humidity Cycling, maximum 0.1 dB/km

Water Immersion, maximum 0.10 dB/km @ 23 °C

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes

Temperature Dependence, maximum Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

Temperature Humidity Cycling, maximum Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

up to 95% relative humidity

COMMSCOPE®