
760229195 | N-012-MP-5K-F20AQ/E



Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser Light Duty Interconnect, 12 fiber, Multimode OM4, Feet jacket marking, Aqua jacket color, Eca flame rating

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

Portfolio CommScope®

Product Type Fiber indoor cable

Product Series N-MP

General Specifications

Cable Type MPO trunk cable

Construction Type Non-armored

Subunit Type Gel-free

Jacket Color Aqua


Jacket Marking Feet

Total Fiber Count 12

Dimensions

Diameter Over Armor 2 mm | 0.079 in

Representative Image



Page 1 of 3



760229195 | N-012-MP-5K-F20AQ/E

Mechanical Specifications

Minimum Bend Radius, loaded38 mm | 1.496 inMinimum Bend Radius, unloaded16 mm | 0.63 inTensile Load, long term, maximum33 N | 7.419 lbfTensile Load, short term, maximum111 N | 24.954 lbf

Compression 4 N/mm | 22.841 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 0.74 N-m | 6.55 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 500 m | 1,640.42 ft

Optical Specifications

Fiber Type OM4, LazrSPEED® 550 | OM4, LazrSPEED® 550

Environmental Specifications

Installation temperature $0 \, ^{\circ}\text{C} \, \text{to} +60 \, ^{\circ}\text{C} \, (+32 \, ^{\circ}\text{F} \, \text{to} +140 \, ^{\circ}\text{F})$ Operating Temperature $0 \, ^{\circ}\text{C} \, \text{to} +70 \, ^{\circ}\text{C} \, (+32 \, ^{\circ}\text{F} \, \text{to} +158 \, ^{\circ}\text{F})$ Storage Temperature $-40 \, ^{\circ}\text{C} \, \text{to} +70 \, ^{\circ}\text{C} \, (-40 \, ^{\circ}\text{F} \, \text{to} +158 \, ^{\circ}\text{F})$

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire Performance Eca

Environmental Space Low Smoke Zero Halogen (LSZH) | Riser

Flame Test Listing NEC OFNR-ST1 (ETL) and c(ETL)

Flame Test Method | IEC 60332-3 | IEC 60754-2 | IEC 61034-2 | UL 1666 | UL 1685

Environmental Test Specifications

Heat Age 0 °C to +85 °C (+32 °F to +185 °F)

COMMSCSPE®

760229195 | N-012-MP-5K-F20AQ/E

Heat Age Test Method IEC 60794-1 F9

Low High Bend 0 °C to +70 °C (+32 °F to +158 °F)

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle 0 °C to +70 °C (+32 °F to +158 °F)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 3.7 kg/km | 2.486 lb/kft

Regulatory Compliance/Certifications

| Agency | Classification |
|---------|---------------------------|
| CENELEC | EN 50575 compliant Declar |

CENELEC EN 50575 compliant, Declaration of Performance (DoP) available

CHINA-ROHS Below maximum concentration value

01---if:--+i--

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system
REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

CS-5K-MP – LazrSPEED® 550 OM4 Bend-Insensitive Multimode

Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

