

Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser Distribution, 12 fiber single-unit, Multimode OM5, Feet jacket marking, Lime green jacket color, Dca flame rating

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

Portfolio CommScope®

Product Type Fiber indoor cable

Product Series N-DS

General Specifications

Cable TypeDistribution

Construction Type Non-armored

Subunit Type Gel-free

Jacket Color Lime green

Jacket Marking Feet


Total Fiber Count 12

Dimensions

Diameter Over Jacket 6.07 mm | 0.239 in

Representative Image





Mechanical Specifications

Minimum Bend Radius, loaded 91 mm | 3.583 in

Minimum Bend Radius, unloaded 61 mm | 2.402 in

Tensile Load, long term, maximum 200 N | 44.962 lbf

Tensile Load, short term, maximum 667 N | 149.948 lbf **Compression** 10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 100 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 500 m | 1,640.42 ft

Optical Specifications

Fiber Type OM5, LazrSPEED® wideband | OM5, LazrSPEED® wideband

Environmental Specifications

Installation temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Operating Temperature $-20 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-4 $^{\circ}\text{F}$ to +158 $^{\circ}\text{F}$)

Page 2 of 4



Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire PerformanceDcaEN50575 CPR Cable EuroClass Smoke Ratings1aEN50575 CPR Cable EuroClass Droplets Ratingd1EN50575 CPR Cable EuroClass Acidity Ratinga2

Environmental Space Low Smoke Zero Halogen (LSZH) | Riser

Flame Test Listing NEC OFNR-ST1 (ETL) and c(ETL)

Flame Test Method | IEC 60332-3 | IEC 60754-2 | IEC 61034-2 | UL 1666 | UL 1685

Environmental Test Specifications

Heat Age $-20 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ $(-4 \,^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F})$

Heat Age Test Method IEC 60794-1 F9

Low High Bend -10 °C to +60 °C (+14 °F to +140 °F)

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle $-20 \,^{\circ}\text{C to} +70 \,^{\circ}\text{C} \left(-4 \,^{\circ}\text{F to} +158 \,^{\circ}\text{F}\right)$

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 34 kg/km | 22.847 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CENELEC EN 50575 compliant, Declaration of Performance (DoP) available

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

CS-5G-TB - LazrSPEED® OM5 WideBand Multimode

Fiber



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable