


# 760237424 | Z-144-LZ-8W-F12BK/20G



Fiber indoor/outdoor cable, TeraSPEED® Inner LSZH, Mini Stranded Loose Tube, 144 fiber, Riser Rated, Gel-filled Subunits with Aluminum Interlocking Armor, Singlemode G.652.D and G.657.A1, Feet jacket marking, Black jacket color

## Product Classification

|                       |   |
|-----------------------|---|
| Regional Availability | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| Portfolio             | CommScope®  |
| Product Type          | Fiber indoor/outdoor cable  |
| Product Series        | Z-LZ  |


## General Specifications

|                              |                       |
|------------------------------|-----------------------|
| Armor Type                   | Interlocking aluminum |
| Cable Type                   | Stranded loose tube   |
| Construction Type            | Armored               |
| Subunit Type                 | Gel-filled            |
| Jacket Color                 | Black                 |
| Jacket Marking               | Feet                  |
| Subunit, quantity            | 12                    |
| Fibers per Subunit, quantity | 12                    |
| Total Fiber Count            | 144                   |

## Dimensions

|                              |                  |
|------------------------------|------------------|
| Buffer Tube/Subunit Diameter | 2 mm   0.079 in  |
| Diameter Over Armor          | 21 mm   0.827 in |
| Diameter Over Jacket         | 23 mm   0.906 in |

## Representative Image



Mechanical Specifications

|                                   |                                       |
|-----------------------------------|---------------------------------------|
| Minimum Bend Radius, loaded       | 460 mm   18.11 in                     |
| Minimum Bend Radius, unloaded     | 322 mm   12.677 in                    |
| Tensile Load, long term, maximum  | 400 N   89.924 lbf                    |
| Tensile Load, short term, maximum | 1335 N   300.12 lbf                   |
| Compression                       | 85 N/mm   485.363 lb/in               |
| Compression Test Method           | FOTP-41   IEC 60794-1 E3              |
| Flex                              | 25 cycles                             |
| Flex Test Method                  | FOTP-104   IEC 60794-1 E6             |
| Impact                            | 35 N-m   309.776 in lb                |
| Impact Test Method                | FOTP-25   IEC 60794-1 E4              |
| Strain                            | See long and short term tensile loads |
| Strain Test Method                | FOTP-33   IEC 60794-1 E1              |
| Twist                             | 10 cycles                             |
| Twist Test Method                 | FOTP-85   IEC 60794-1 E7              |
| Vertical Rise, maximum            | 89 m   291.995 ft                     |

Optical Specifications

|            |  |
|------------|--|
| Fiber Type | G.652.D and G.657.A1, TeraSPEED®   OS2   OS2 |
|------------|--|

Environmental Specifications

|                          |                                      |
|--------------------------|--------------------------------------|
| Installation temperature | -30 °C to +60 °C (-22 °F to +140 °F) |
| Operating Temperature    | -40 °C to +70 °C (-40 °F to +158 °F) |

760237424 | Z-144-LZ-8W-F12BK/20G

|                               |  |
|-------------------------------|--|
| Storage Temperature           | -40 °C to +75 °C (-40 °F to +167 °F)                                 |
| Cable Qualification Standards | ANSI/ICEA S-104-696   EN 187105   Telcordia GR-20   Telcordia GR-409 |
| Environmental Space           | Buried   Low Smoke Zero Halogen (LSZH)   Riser                       |
| Flame Test Listing            | NEC OFCR-ST1 (ETL) and c(ETL)  |
| Flame Test Method             | IEC 60332-3   IEC 60754-2   IEC 61034-2   UL 1666   UL 1685          |
| Jacket UV Resistance          | UV stabilized  |
| Water Penetration             | 24 h   |
| Water Penetration Test Method | FOTP-82   IEC 60794-1 F5   |

Environmental Test Specifications

|                               |                                      |
|-------------------------------|--------------------------------------|
| Cable Freeze                  | -2 °C   28.4 °F                      |
| Cable Freeze Test Method      | FOTP-98   IEC 60794-1 F15            |
| Drip                          | 70 °C   158 °F                       |
| Drip Test Method              | FOTP-81   IEC 60794-1 E14            |
| Heat Age                      | -40 °C to +85 °C (-40 °F to +185 °F) |
| Heat Age Test Method          | IEC 60794-1 F9                       |
| Low High Bend                 | -30 °C to +60 °C (-22 °F to +140 °F) |
| Low High Bend Test Method     | FOTP-37   IEC 60794-1 E11            |
| Temperature Cycle             | -40 °C to +70 °C (-40 °F to +158 °F) |
| Temperature Cycle Test Method | FOTP-3   IEC 60794-1 F1              |

Packaging and Weights

|              |                            |
|--------------|----------------------------|
| Cable weight | 460 kg/km   309.106 lb/kft |
|--------------|----------------------------|

Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| CENELEC       | EN 50575 compliant, Declaration of Performance (DoP) available   |
| CHINA-ROHS    | Below maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |



## Included Products

CS-8W-IOLT – TeraSPEED® OS2 Singlemode Fiber

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

TeraSPEED®

TeraSPEED® OS2 Singlemode Fiber

Product Classification

|              |               |
|--------------|---------------|
| Portfolio    | CommScope®    |
| Product Type | Optical fiber |

General Specifications

|   |                        |
|---|------------------------|
| Cladding Diameter                             | 125 µm                 |
| Cladding Diameter Tolerance                   | ±0.7 µm                |
| Cladding Non-Circularity, maximum             | 0.7 %                  |
| Coating Diameter (Colored)                    | 249 µm                 |
| Coating Diameter (Uncolored)                  | 242 µm                 |
| Coating Diameter Tolerance (Colored)          | ±13 µm                 |
| Coating Diameter Tolerance (Uncolored)        | ±5 µm                  |
| Coating/Cladding Concentricity Error, maximum | 12 µm                  |
| Core Diameter                                 | 8.3 µm                 |
| Core/Clad Offset, maximum                     | 0.5 µm                 |
| Proof Tensile Stress                          | 100,000 psi (0.69 GPa) |

Dimensions

|                     |                 |
|---------------------|-----------------|
| Fiber Curl, minimum | 4 m   13.123 ft |
|---------------------|-----------------|

Mechanical Specifications

|  |   |
|--|---|
| Macrobending, 20 mm Ø mandrel, 1 turn    | 0.75 dB @ 1,550 nm   1.50 dB @ 1,625 nm |
| Macrobending, 30 mm Ø mandrel, 10 turns  | 0.25 dB @ 1,550 nm   1.00 dB @ 1,625 nm |
| Macrobending, 60 mm Ø mandrel, 100 turns | 0.05 dB @ 1,550 nm   0.05 dB @ 1,625 nm |
| Coating Strip Force, maximum             | 8.9 N   2.001 lbf                       |
| Coating Strip Force, minimum             | 1.3 N   0.292 lbf                       |
| Dynamic Fatigue Parameter, minimum       | 20                                      |

# CS-8W-IOLT

## Optical Specifications

|                                     |                     |
|-------------------------------------|---------------------|
| Cabled Cutoff Wavelength, maximum   | 1260 nm             |
| Point Defects, maximum              | 0.1 dB              |
| Zero Dispersion Slope, maximum      | 0.092 ps/[km-nm-nm] |
| Zero Dispersion Wavelength, maximum | 1324 nm             |
| Zero Dispersion Wavelength, minimum | 1300 nm             |

## Optical Specifications, Wavelength Specific

|   |   |
|---|---|
| Attenuation, maximum                                    | 0.22 dB/km @ 1,550 nm   0.25 dB/km @ 1,490 nm   0.25 dB/km @ 1,625 nm   0.36 dB/km @ 1,310 nm   0.36 dB/km @ 1,385 nm |
| Attenuation, typical                                    | 0.19 dB/km @ 1,550 nm   0.33 dB/km @ 1,310 nm   |
| Backscatter Coefficient                                 | -79.6 dB @ 1,310 nm   -82.1 dB @ 1,550 nm   |
| Dispersion, maximum                                     | 18 ps(nm-km) at 1550 nm   3.5 ps(nm-km) from 1285 nm to 1330 nm at 1310 nm  |
| Index of Refraction                                     | 1.467 @ 1,310 nm   1.467 @ 1,385 nm   1.468 @ 1,550 nm  |
| Mode Field Diameter                                     | 10.4 μm @ 1,550 nm   9.2 μm @ 1,310 nm   9.6 μm @ 1,385 nm  |
| Mode Field Diameter Tolerance                           | ±0.4 μm @ 1310 nm   ±0.5 μm @ 1550 nm   ±0.6 μm @ 1385 nm   |
| Polarization Mode Dispersion Link Design Value, maximum | 0.04 ps/sqrt(km)  |
| Standards Compliance                                    | ITU-T G.652.D   ITU-T G.657.A1   TIA-492CAAB (OS2)  |

## Environmental Specifications

|                                       |                    |
|---------------------------------------|--------------------|
| Heat Aging, maximum                   | 0.05 dB/km @ 85 °C |
| Temperature Dependence, maximum       | 0.05 dB/km         |
| Temperature Humidity Cycling, maximum | 0.05 dB/km         |
| Water Immersion, maximum              | 0.05 dB/km @ 23 °C |

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

## \* Footnotes

# CS-8W-IOLT

---

|  |   |
|--|---|
| <b>Temperature Dependence, maximum</b>       | Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)                                   |
| <b>Temperature Humidity Cycling, maximum</b> | Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F) up to 95% relative humidity |