


LazrSPEED® Low Smoke Zero Halogen Riser Distribution Cable, 24 fiber single-unit, OM3, white



Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio

CommScope®

Product Type

Fiber indoor cable

General Specifications

Cable Type

Distribution

Construction Type

Non-armored

Fiber Type, quantity

24

Jacket Color

White

Subunit Type

Gel-free

Total Fiber Count


24

Dimensions

Diameter Over Jacket

8.6 mm | 0.339 in

Representative Image



Mechanical Specifications

Minimum Bend Radius, loaded	130 mm 5.118 in
Minimum Bend Radius, unloaded	86 mm 3.386 in
Tensile Load, long term, maximum	400 N 89.924 lbf
Tensile Load, short term, maximum	1335 N 300.12 lbf
Compression	10 N/mm 57.101 lb/in
Compression Test Method	FOTP-41 IEC 60794-1 E3
Flex	100 cycles
Flex Test Method	FOTP-104 IEC 60794-1 E6
Impact	5.88 N-m 52.042 in lb
Impact Test Method	FOTP-25 IEC 60794-1 E4
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33 IEC 60794-1 E1
Twist	10 cycles
Twist Test Method	FOTP-85 IEC 60794-1 E7
Vertical Rise, maximum	500 m 1,640.42 ft

Optical Specifications

Fiber Type	OM3, LazrSPEED® 300 OM3, LazrSPEED® 300
-------------------	---

Environmental Specifications

760239670 | N-024-DS-5L-FSUWH/D

Installation temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Operating Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Cable Qualification Standards	ANSI/ICEA S-83-596 Telcordia GR-409
EN50575 CPR Cable EuroClass Fire Performance	Dca
EN50575 CPR Cable EuroClass Smoke Rating	s1a
EN50575 CPR Cable EuroClass Droplets Rating	d1
EN50575 CPR Cable EuroClass Acidity Rating	a1
Environmental Space	Low Smoke Zero Halogen (LSZH) Riser
Flame Test Listing	NEC OFNR-LS (ETL) and c(ETL)
Flame Test Method	IEC 60332-3 IEC 60754-2 IEC 61034-2 IEEE 383 UL 1666 UL 1685

Environmental Test Specifications

Heat Age	-20 °C to +85 °C (-4 °F to +185 °F)
Heat Age Test Method	IEC 60794-1 F9
Low High Bend	-10 °C to +60 °C (+14 °F to +140 °F)
Low High Bend Test Method	FOTP-37 IEC 60794-1 E11
Temperature Cycle	-20 °C to +70 °C (-4 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3 IEC 60794-1 F1

Packaging and Weights

Cable weight	66 kg/km 44.35 lb/kft
---------------------	-------------------------

Regulatory Compliance/Certifications

Agency	Classification
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



Included Products

CS-5L-TB	– LazrSPEED® 300 OM3 Bend-Insensitive Multimode Fiber
----------	---

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

LazrSPEED® 300

Product Classification

Portfolio	CommScope®
Product Type	Optical fiber

General Specifications

Cladding Diameter	125 µm
Cladding Diameter Tolerance	±0.8 µm
Cladding Non-Circularity, maximum	1 %
Coating Diameter (Colored)	254 µm
Coating Diameter (Uncolored)	245 µm
Coating Diameter Tolerance (Colored)	±7 µm
Coating Diameter Tolerance (Uncolored)	±10 µm
Coating/Cladding Concentricity Error, maximum	12 µm
Core Diameter	50 µm
Core Diameter Tolerance	±2.5 µm
Core/Clad Offset, maximum	1.5 µm
Proof Test	689.476 N/mm ² 100000 psi
Tight Buffer Diameter	900 µm
Tight Buffer Diameter Tolerance	±40 µm

Mechanical Specifications

Macrobending, 15 mm mandrel, 2 turns	0.20 dB @ 850 nm 0.50 dB @ 1,300 nm
Macrobending, 30 mm mandrel, 2 turns	0.10 dB @ 850 nm 0.30 dB @ 1,300 nm
Coating Strip Force, maximum	8.9 N 2.001 lbf
Coating Strip Force, minimum	1.3 N 0.292 lbf

CS-5L-TB

Dynamic Fatigue Parameter, minimum 18

Optical Specifications

Numerical Aperture 0.2
Numerical Aperture Tolerance ± 0.015
Point Defects, maximum 0.15 dB
Zero Dispersion Slope, maximum 0.105 ps/[km-nm-nm]
Zero Dispersion Wavelength, maximum 1316 nm
Zero Dispersion Wavelength, minimum 1297 nm

Optical Specifications, Wavelength Specific

1 Gbps Ethernet Distance 1,020 m @ 850 nm | 600 m @ 1,300 nm
10 Gbps Ethernet Distance 300 m @ 850 nm
Attenuation, maximum 1.00 dB/km @ 1,300 nm | 3.00 dB/km @ 850 nm
Backscatter Coefficient -68.0 dB @ 850 nm | -75.7 dB @ 1,300 nm
Bandwidth, Laser, minimum 2,000 MHz-km @ 850 nm | 500 MHz-km @ 1,300 nm
Bandwidth, OFL, minimum 1,500 MHz-km @ 850 nm | 500 MHz-km @ 1,300 nm
Differential Mode Delay 0.70 ps/m @ 850 nm | 0.88 ps/m @ 1,300 nm
Differential Mode Delay Note Superior to TIA-492AAAC and IEC 60793-2-10 at 850 nm
Index of Refraction 1.479 @ 1,300 nm | 1.483 @ 850 nm
Standards Compliance TIA-492AAAC (OM3)

Environmental Specifications

Heat Aging, maximum 0.20 dB/km @ 85 °C
Temperature Dependence, maximum 0.1 dB/km
Temperature Humidity Cycling, maximum 0.2 dB/km
Water Immersion, maximum 0.20 dB/km @ 23 °C

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



CS-5L-TB

* Footnotes

- Temperature Dependence, maximum** Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)
- Temperature Humidity Cycling, maximum** Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F) up to 95% relative humidity