

Fiber indoor/outdoor cable, TeraSPEED®, Single Jacket/Single Armor, Low Smoke Zero Halogen (LSZH), 12 fiber, Singlemode G.652.D and G. 657.A1, Gel Filled, Stranded Loose Tube, Meters jacket marking, Black jacket color, B2ca flame rating

 Corrugated steel tape armor is strong yet flexible, providing additional crush and rodent protection

Product Classification

Regional Availability EMEA

Portfolio CommScope®

Product Type Fiber indoor/outdoor cable

Product Series C-LA

General Specifications

Armor Type Corrugated steel

Cable Type Stranded loose tube

Construction TypeArmoredSubunit TypeGel-filledJacket ColorBlack

Jacket Marking Method Meters

Jacket Marking Method Inkjet

Jacket Marking Text COMMSCOPE GB OPTICAL CABLE OS2 SM 12 FIBER EN50575 CLASS B

[SERIAL NUMBER] [MM/YY] [METRE MARK]

Subunit, quantity 6

Fibers per Subunit, quantity 12


Total Fiber Count 12

Dimensions

Buffer Tube/Subunit Diameter 2 mm | 0.079 in **Diameter Over Jacket** 12.3 mm | 0.484 in

Representative Image





Mechanical Specifications

Minimum Bend Radius, loaded 200 mm | 7.874 in

Minimum Bend Radius, unloaded133 mm5.236 inTensile Load, long term, maximum800 N179.847 lbf

Tensile Load, short term, maximum 2700 N | 606.984 lbf

Compression 44 N/mm | 251.246 lb/in

Compression Test Method IEC 60794-1 E3

Flex 25 cycles

Flex Test Method IEC 60794-1 E6

Impact 10 N-m | 88.507 in lb

Impact Test Method IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method IEC 60794-1 E7

Vertical Rise, maximum 432 m | 1,417.323 ft

Optical Specifications

Fiber Type G.652.D and G.657.A1, TeraSPEED® | OS2 | OS2

Environmental Specifications

Installation temperature -30 °C to +60 °C (-22 °F to +140 °F)

Page 2 of 4

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+75 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+167 \,^{\circ}\text{F}$)

Cable Qualification Standards EN 187105 | IEC 60794-1-2

EN50575 CPR Cable EuroClass Fire PerformanceB2caEN50575 CPR Cable EuroClass Smoke Ratings1aEN50575 CPR Cable EuroClass Droplets Ratingd0EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Aerial, lashed | Buried | Low Smoke Zero Halogen (LSZH)

Flame Test Method | IEC 60332-1-2 | IEC 60754-2 | IEC 61034-2

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method IEC 60794-1 F5

Environmental Test Specifications

Cable Freeze-2 °C | 28.4 °FCable Freeze Test MethodIEC 60794-1 F15

Heat Age -40 °C to +85 °C (-40 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-30 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-22 $^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Low High Bend Test Method IEC 60794-1 E11

Temperature Cycle $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Temperature Cycle Test Method IEC 60794-1 F1

Packaging and Weights

Cable weight 199.4 kg/km | 133.991 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CENELEC EN 50575 compliant, Declaration of Performance (DoP) available

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant





Included Products

CS-8W-250-EMEA – LightScope® ZWP Singlemode Fiber 8W-250um

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

