

Fiber indoor/outdoor cable, TeraSPEED®, Mini Single Jacket, All-Dielectric, Low Smoke Zero Halogen (LSZH), 24 fiber, Singlemode G.657. A2, Gel-Filled, Stranded Loose Tube, Black jacket color, Meters cable marking, Eca flame rating

Product Classification

Regional Availability EMEA

Portfolio CommScope®

Product Type Fiber indoor/outdoor cable

Product Series C-I N

General Specifications

Cable Type Stranded loose tube

Non-armored **Construction Type**

Gel-filled **Subunit Type**

4 Filler, quantity

Jacket Color Black **Jacket Marking** Meters **Jacket Marking Method** Inkjet

Jacket Marking Text COMMSCOPE GB OPTICAL CABLE G657A2 SM 24 FIBER EN50575 CLASS

24

E [SERIAL NUMBER] [MM/YY] [METRE MARK]


2 Subunit, quantity 12 Fibers per Subunit, quantity **Total Fiber Count**

Dimensions

Buffer Tube/Subunit Diameter 2 mm | 0.079 in **Diameter Over Jacket** 11 mm | 0.433 in

Representative Image





Mechanical Specifications

Minimum Bend Radius, loaded165 mm6.496 inMinimum Bend Radius, unloaded110 mm4.331 in

Tensile Load, long term, maximum 800 N | 179.847 lbf

Tensile Load, short term, maximum 2700 N | 606.984 lbf

Compression 22 N/mm | 125.623 lb/in

Compression Test Method IEC 60794-1 E3

Flex 25 cycles

Flex Test Method IEC 60794-1 E6

Impact 10 N-m | 88.507 in lb

Impact Test Method IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method IEC 60794-1 E1

Twist 10 cycles

Twist Test Method IEC 60794-1 E7

Vertical Rise, maximum 643 m | 2,109.58 ft

Optical Specifications

Fiber Type G.657.A2 | G.657.A2

Environmental Specifications

Installation temperature $-30 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-22 $^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

COMMSCOPE®

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+75 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+167 \,^{\circ}\text{F}$)

Cable Qualification Standards EN 187105 | IEC 60794-1-2

EN50575 CPR Cable EuroClass Fire Performance Eca

Environmental Space Aerial, lashed | Buried | Low Smoke Zero Halogen (LSZH)

Flame Test Method | IEC 60332-1-2 | IEC 60754-2 | IEC 61034-2

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method IEC 60794-1 F5

Environmental Test Specifications

Cable Freeze -2 °C | 28.4 °F

Cable Freeze Test Method IEC 60794-1 F15

Drip 70 °C | 158 °F

Drip Test Method IEC 60794-1 E14

Heat Age $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-30 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-22 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

Low High Bend Test Method IEC 60794-1 E11

Temperature Cycle $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Temperature Cycle Test Method IEC 60794-1 F1

Packaging and Weights

Cable weight 127 kg/km | 85.34 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CENELEC EN 50575 compliant, Declaration of Performance (DoP) available

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant





Included Products

CS-8G-LT

 Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T G.657.A2, B2)

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

