F187CCS2



FlexTwist® Flexible Twist for WR187, 3.95–5.85 GHz, with interface types CPR187G and CPR187G, 600 mm

Product Classification

Product TypeRectangular waveguide, flexible twist

Product Brand FlexTwist®

General Specifications

ComponentFlexible TwistInterfaceCPR187GInterface 2CPR187G

Dimensions

 Length
 600 mm | 23.622 in

 Waveguide Size
 WR187 | WG12 | R48

Electrical Specifications

 $\textbf{Attenuation} \hspace{1.5cm} 0.17 \hspace{.1cm} \text{dB/m} \hspace{.1cm} \mid \hspace{.1cm} 0.052 \hspace{.1cm} \text{dB/ft}$

Average Power 3000 W

Operating Frequency Band 3.95 – 5.85 GHz

Peak Power 1250 kW

VSWR 1.1

Mechanical Specifications

Minimum Bend Radius, Multiple Bends (E Plane)165 mm | 6.496 inMinimum Bend Radius, Multiple Bends (H Plane)330 mm | 12.992 inMaximum Twist165 °/m | 50.292 °/ftPressurization, maximum0.207 N/mm² | 30 psi



F187CCS2

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

